

# SAVE 10%\*, GET FREE SHIPPING AND FREE GLASS BEAD ABRASIVE!

WITH PURCHASE OF ANY PRODUCT SHOWN BELOW



Special promo runs from October 8 to December 31, 2020. \*Savings are up to 10%.



**B2247283** 36" Wide, with Trigger Gun\*  
**B2247134** 36" Wide  
**B2247164** 36" Wide, with LED Light Kit



**B2247285** 48" Wide (foot pedal not included)  
**B2247122** 48" Wide  
**B2247163** 48" Wide, with LED Light Kit



**B2247121** 60" Wide  
**B2247135** 60" Wide, with LED Light Kit

## ALC PROFESSIONAL STEEL BLAST CABINETS

Proudly Made in the USA



- Heavy-duty 14 gauge steel with welded seams
- Includes foot pedal gun (except B2247283 which includes trigger gun) & 150 watt light kit (B2247164, B2247163 & B2247135 includes LED light kit)
- High quality lined 24" gloves and cushioned foam armholes
- 112 CFM dust collector included with all steel cabinets
- Includes protective window underlay
- Full opening top door and side door
- Operating PSI: 80-125
- Air Consumption CFM @ 80 psi: 7-20
- Grate Capacity: 200 lbs.
- Abrasive Capacity Minimum: 25 lbs.
- 2 Year Warranty

Model No.	Work Area (WxHxD)	Main Door Opening	Side Door Opening	Window Dimension	Door Open Height	Overall Dim. (WxHxD)	Weight	Price
B2247283	36"x24"x24"	13"x35"	11"x17"	24"x12"	75"	36"x60"x24"	270 lbs.	<b>\$1,435.00</b>
B2247134	36"x24"x24"	13"x35"	11"x17"	24"x12"	75"	36"x60"x24"	270 lbs.	<b>\$1,515.00</b>
B2247164	36"x24"x24"	13"x35"	11"x17"	24"x12"	75"	36"x60"x24"	270 lbs.	<b>\$1,889.00</b>
B2247285	48"x24"x24"	13"x47"	11"x17"	24"x12"	75"	48"x60"x24"	303 lbs.	<b>\$1,699.00</b>
B2247122	48"x24"x24"	13"x47"	11"x17"	24"x12"	75"	48"x60"x24"	303 lbs.	<b>\$1,777.00</b>
B2247163	48"x24"x24"	13"x47"	11"x17"	24"x12"	75"	48"x60"x24"	303 lbs.	<b>\$1,999.00</b>
B2247121	60"x24"x24"	13"x59"	11"x17"	(2) 24"x12"	75"	60"x60"x24"	333 lbs.	<b>\$1,999.00</b>
B2247135	60"x24"x24"	13"x59"	11"x17"	(2) 24"x12"	75"	60"x60"x24"	333 lbs.	<b>\$2,299.00</b>



**B2247205** 36" Wide  
**B2247284** 36" Wide, with foot pedal



**B2247211** 36" Wide  
**B2247210** 36" Wide, with foot pedal



**B2247208** 36" Wide  
**B2247209** 36" Wide, with foot pedal

## ALC POLYMER BLAST CABINETS

Proudly Made in the USA



- One-piece construction (no leaks)
- Self-adhesive protective window underlay
- Pistol grip siphon gun
- B2247208/B2247209 feature heavy-duty 14 gauge steel legs
- Recommended use with shop vacuum as dust collector (not provided)
- B2247208/B2247209 include a standard light kit
- Operating PSI: 80-110
- Air Consumption CFM @ 80 psi: 7-20
- Grate Capacity: 35 lbs.
- 2 Year Warranty

Model No.	Includes Foot Pedal	Work Area (WxHxD)	Door Opening	Window Dimension	Abrasive Capacity Min.	Overall Dim. (WxHxD)	Weight	Price
B2247205	No	22"x12"x18"	14"x29"	16"x20"	10 lbs.	24"x21"x19"	25 lbs	<b>\$248.00</b>
B2247284	Yes	22"x12"x18"	14"x29"	16"x20"	10 lbs.	24"x21"x19"	25 lbs	<b>\$375.00</b>
B2247211	No	30"x27"x20"	15"x27"	15"x27"	10 lbs.	31"x28"x21"	34 lbs	<b>\$359.00</b>
B2247210	Yes	30"x27"x20"	15"x27"	15"x27"	10 lbs.	31"x28"x21"	34 lbs	<b>\$499.00</b>
B2247208	No	35"x23"x23"	15"x33"	15"x33"	25 lbs.	38"x58"x24"	81 lbs	<b>\$529.00</b>
B2247209	Yes	35"x23"x23"	15"x33"	15"x33"	25 lbs.	38"x58"x24"	81 lbs	<b>\$719.00</b>