

V-Series Standard Lanyards

Technical Data Sheet



CAPACITY	ANSI Z 359.13: 130 lb.–310 lb. (59–140 kg) CSA Z259.11: 150 lb.–310 lb. (68–140 kg) CSA Z259.11 Light Weight: 110 lb.–230 lb. (50–105 kg)
BRAND	MSA
SUB BRAND/MODEL NAME	V-Series Standard Shock Absorbing Lanyard
THREAD/STITCHING	Polyester
WEB MATERIAL	Polyester
SNAPHOOK MATERIAL	Steel
PRODUCT WEIGHT	2.35–5.73 lb.
SHIPPING WEIGHT	2.35–5.73 lb.
SHIPPING DIMENSIONS	5"x1" – 6"x1"
PRODUCT STYLES	Single & Twin, Fixed & Adjustable, Tie-back
STANDARDS	ANSI Z359.13, CSA Z259.11–17, OSHA

PART NO.	Snaphook(s)	Type						Standards			
		Single-Leg	Twin-Leg	Tie-back	Adjustable	Fixed	Length	ANSI Z359.13	CSA Z259.11-17	CSA Z259.11-17 Lightweight Worker	OSHA
10191755	SM	■			■		6'	■			■
10191756	SM		■		■		6'	■			■
10191757	LG	■			■		6'	■			■
10191758	LG		■		■		6'	■			■
10193124	SM	■				■	3'	■			■
10193125	SM	■				■	4'	■			■
10193128	SM	■		■			6'	■			■
10193129	SM		■	■			6'	■			■
10188100	SM	■			■		6'		■		■
10188102	SM		■		■		6'		■		■
10188103	LG	■			■		6'		■		■
10188101	LG		■		■		6'		■		■
10190397	SM	■			■		6'			■	■
10190399	SM		■		■		6'			■	■
10190398	LG	■			■		6'			■	■
10190400	LG		■		■		6'			■	■
10193126	SM	■				■	3'		■		■
10193127	SM	■				■	4'		■		■
10193130	SM	■		■			6'		■		■
10193151	SM		■	■			6'		■		■

PART NO.	Snaphook	Type	Standards		
		Energy-Absorber with D-ring	ANSI Z359.13	CSA Z259.11-17	OSHA
10193154	SM	■	■		■
10193155	SM	■		■	■



Note: This Bulletin contains only a general description of the products shown. While uses and performance capabilities are described, under no circumstances shall the products be used by untrained or unqualified individuals and not until the product instructions including any warnings or cautions provided have been thoroughly read and understood. Only they contain the complete and detailed information concerning proper use and care of these products.



MSA – The Safety Company
 1000 Cranberry Woods Drive
 Cranberry Township, PA 16066 USA
 Phone 724-776-8600
www.MSAafety.com
U.S. Customer Service Center
 Phone 1-800-MSA-2222
 Fax 1-800-967-0398

MSA Canada
 Phone 1-800-672-2222
 Fax 1-800-967-0398
MSA Mexico
 Phone 01 800 672 7222