


**RESTORATIVE CARPET CLEANING**



The Galaxy Pro is a 17 gallon portable carpet extractor with a powerful dual vacuum system that comes standard from the factory “heat ready” for optimum carpet cleaning performance. Versatility is the name of the game with the “heat ready” system. You can purchase the machine without heat and later decide to add heat without having to buy a new unit.

**UPHOLSTERY & SPOT CLEANING**



**HEAT READY**

The Galaxy Pro is manufactured with the ability to easily add the Heat ‘N’ Run 2000 Watt external heater to the machine at anytime. Using hot water when cleaning carpet with an extractor increases cleaning results and productivity dramatically, and reduces the overall cost of cleaning. On-demand heat is a must have option to clean heavily soiled carpets.

The external heater also keeps heat away from the internal electrical components, extending the life of the machine and makes maintenance or repairs a snap.

*Watch the Galaxy  
Series Video on Your  
Phone*



**Features & Benefits**

- Exclusive “heat ready” system offers the ultimate in versatility
- External heater makes repairs a snap and keeps heat away from the electrical components in the motor compartment.
- Clean “granite look” projects an image of professionalism and keeps the machine looking brand new.
- Upright-mounted vacuum motors along with a special intercooler guarantee long life and durability
- Standard 5-gallon bucket fits under drain valve for easy emptying
- Opens quickly like a clamshell for easy servicing
- Top-mounted switches
- Sealed motor cavity insures that spills on the outside stay out
- Detachable cord makes it easy to drop the cord and wheel the machine to a drain or toilet for emptying
- Galaxy Pro CX offers 500 psi, dual 3-stage vacs, 185” lift all on a single cord



**Specifications**

Model	B2305411	B2305410*
Solution Tank	17 gallon	17 gallon
Recovery Tank	15 gallon	15 gallon
Solution Pressure	220 psi	500 psi
Vacuum Motor	Dual, high performance 3-stage	Dual, high performance 3-stage
Waterlift	190"	190"
Tank Construction	Polyethylene	Polyethylene
Baseplate	¼" aluminum	¼" aluminum
Rear Wheels	10" non-marking	10" non-marking
Front Casters	4" locking	4" locking
Power Cord	50 ft. detachable	50 ft. detachable
Dimensions	38"H x 31"L x 20"W	38"H x 31"L x 20"W
Weight	95 lbs.	104 lbs.
Shipping Weight	111 lbs.	120 lbs.
Shipping Dimensions	40.5"H x 39"L x 21"W	40.5"H x 39"L x 21"W
Electrical Draw	15.4 amps	17.1 amps
Warranty	5 years parts & Labor, lifetime on enclosure	5 years parts & Labor, lifetime on enclosure

\*20 amp circuit required

**Optional Carpet & Hard Surface Tools**



B2305460



Heat 'N' Run External Heater  
B2305459



B2305441



B2305455



B2305446

Manufactured in the USA by:

