



Superior Water Recovery Lightweight | Compact Durable Construction

The new, super-duty high volume, FloodBuster flood pumper makes quick work of the toughest flood restoration jobs. The FloodBuster allows easy transport to and from the job site due to its small size, light weight, and single-person load capabilities into any type of vehicle. Its compact design, with 12" rear wheels, 5" front swivel casters and stair climbing handle design, allows for easy storage in any location.

The FloodBuster moves water at 50 GPM (on a single power cord) by using a powerful sump pump and a wide 1.5" diameter dump hose that outperforms a standard garden hose that comes with other competitor equipment.

When you choose the FloodBuster, you know that you'll have industry leading performance, safety, and water removal in this BEST IN CLASS machine.

*Watch the Video from
Your Phone*



Manufactured in the USA by:

EDIC

Features & Benefits:

- Adjustable handle and large rear wheels make Stair climbing & transport to the job site easy
- Single cord operation
- Ergonomic dolly style design placing the weight over the rear wheels for easy maneuverability
- FloodBuster uses a Heavy duty, powerful, Industrial waste and sewage sump pump that can handle up to 1/2" spherical solids for high performance and long life
- 50 GPM performance makes quick work of any flood situation
- The 12" wheels and 5" casters lift the machine high off the ground
- The FloodBuster is very compact. Cleaning vans are packed with equipment and this gives the contractor a special advantage
- The large easy to access and remove screen basket catches all the debris before it reaches the tank and the pumps. This feature combined with the pumps ability to handle large diameter debris insures trouble free operation for long periods of time
- Top, front mounted controls are easy to access
- Tough rotationally molded body with a lifetime warranty

Specifications:

Model:	B2305416
Pump GPM	50 GPM
Handles Spherical Solids	Up to ½ inch
Vacuum	5.7" Diameter 3-stage
Air Watts	601
Air Flow	110 CFM
Waterlift	158"
Overfill Vacuum Switch	Yes
Large Tank Opening	Yes
Large Debris Screen Basket	Stainless Steel
Vacuum Hose	1.5" x 25' crushproof vacuum hose
Dump Hose	1.5" x 25' with quick connects
Wand Kit	S-bend carpet & hard floor
Handle	Adjustable for easy stair climbing
Rear Wheels	12" ball bearing, non-marking
Front Casters	5" locking
GFCI	Optional
Ergonomic Dolly Style Design	Yes
Power Cord	Single 25 ft. detachable
Electric Power	18 amps
Weight	101 lbs.
Dimensions	21" W x 29" L x 31.5" H

STANDARD TOOLS

