



RESTORATIVE CARPET CLEANING



UPHOLSTERY & SPOT CLEANING



ON DEMAND HEAT



GALAXY 2000

HEATED PORTABLE CARPET EXTRACTOR



HEAT READY

The 12 gallon Galaxy 2000 carpet extractors come "heat-ready." Life's little decisions just got a whole lot easier! You can purchase any Galaxy without heat and if you change your mind, no problem. Simply order our Heat N'Run external heater, and away you go. Using hot water when cleaning carpet with an extractor increases cleaning results and productivity dramatically, and reduces the overall cost of cleaning. On-demand heat is a must have option to clean heavily soiled carpets.

Placing the heater on the outside of the extractor insures that everything on the inside of the machine runs cooler, extending the life of the vacuum and pump motors. The stainless steel heater tank is guaranteed for life. If a repair is necessary, simply lift the heater off the back of the machine. Meantime, you can continue to use the unit without heat and finish the job!

The Galaxy is very compact. Work vans are packed with equipment and this gives the contractor a special advantage with all this power in a small footprint.

*Watch the Galaxy
Series Video on Your
Phone*



Questions? Contact us at 888.978.7759 or globalindustrial.com

Features & Benefits

- Exclusive heat-ready system offers the ultimate in versatility
- External heater makes repairs a snap and keeps heat away from the motor compartment
- Clean "granite look" projects an image of professionalism and keeps the Galaxy looking sharp
- Upright-mounted motors along with a special intercooler guarantee long life and durability
- Standard 5-gallon bucket fits under drain valve for easy emptying
- Opens quickly like a clamshell for easy servicing
- Top-mounted switches
- Sealed motor cavity insures that spills on the outside stay out
- The Galaxy CX offers 500PSI, Dual 3 Stage Vacs, 185" all on a single cord!
- Exclusive back mounted components make it easier to push the machine out of the way as you move back while cleaning
- The back wheels protect all the components from damage during transport
- 3 sides are totally free of fittings so it's easy to load without damage on either side, the front or on its wheels with the casters locked
- The back wheels protect all the components from damage during transport
- Twist lock cords allow you to drop the cords in place and wheel the machine to a drain or toilet to fill or empty

Specifications

Model	B2305412	B2305413	B2305414 [∞]
Solution Tank	12 gallon	12 gallon	12 gallon
Recovery Tank	11 gallon	11 gallon	11 gallon
Solution Pressure	100 psi	220 psi	500 psi adjustable
Vacuum Motor	Dual 2-stage	Dual 2-stage	Dual 3-stage
Waterlift	150"	150"	190"
Tank Construction	Polyethylene	Polyethylene	Polyethylene
Baseplate	¼" aluminum	¼" aluminum	¼" aluminum
Rear Wheels	10" non-marking	10" non-marking	10" non-marking
Front Casters	4" locking	4" locking	4" locking
Power Cord	50 ft. detachable	50 ft. detachable	50 ft. detachable
Dimensions	35"H x 31"L x 18"W	35"H x 31"L x 18"W	35"H x 31"L x 18"W
Weight	80 lbs.	80 lbs.	89 lbs.
Shipping Weight	96 lbs.	96 lbs.	105 lbs.
Shipping Dimensions	36.5"H x 31.5"L x 19"W	36.5"H x 31.5"L x 19"W	36.5"H x 31.5"L x 19"W
Electrical Draw	13.5 amps	14.1 amps	17.1 amps
Warranty	5 years parts & Labor, lifetime on enclosure	5 years parts & Labor, lifetime on enclosure	5 years parts & Labor, lifetime on enclosure

[∞]20 amp circuit required



Optional Carpet & Hard Surface Tools



Heat 'N' Run External Heater
B2305459



B2305454

B2305455

B2305446

B2305441



B2305460

Manufactured in the USA by: