

ONE PACKS

Dispenser-Free Control Systems®

GS Extra-Strength Cleaner

B2310694

Heavy-Duty All-Purpose Cleaner and Degreaser

Safe Handling

Avoid contact with eyes.

IF IN EYES: Rinse with water for a few minutes. If irritation persists, get medical attention.


Personal Protective Equipment: Wear protective eyewear if contact is possible.

Unused Product Disposal: Unused product or its solutions may be poured down the drain. Never pour unused product or its solutions down an outdoor drain.

Improper dilution or improper use of this product may result in skin and eye irritation, damage to surfaces and unsatisfactory cleaning performance.

Pack Recycling: Empty packs should be rinsed out with water and then placed for recycling where accepted.

DIRECTIONS



Empty contents of GS Extra-Strength Cleaner Concentrate into cold water (see dilution rates below). Apply solution with trigger spray, sponge, or cloth. Wipe away with damp cloth. Empty and rinse bottle before refilling.

Dilutions

#2308534, #2385300, #2313743, #2313767 - Mix each pack with 1 quart of cold water for all-purpose spray-and-wipe cleaning. Mix with 1 gallon of cold water for scrubbing or 2 gallons for damp mopping.

#2384200, #2384204 - Mix with 2 gallons of cold water for scrubbing or 4 gallons for damp mopping.

#2384309 - Mix each pack with 4 gallons of cold water for scrubbing or 8 gallons for damp mopping.



This product meets Green Seal™ Standard GS-37 based on effective performance, concentrated volume, minimized/recycled packaging and protective limits on: VOCs and human & environmental toxicity. GreenSeal.org.

The U.S. EPA's Safer Choice Program helps consumers, businesses, and institutional buyers identify cleaning and other products that perform well and are safer for people and the environment.



ONE PACKS

Dispenser-Free Control Systems®

GS Extra-Strength Cleaner

B2310694

Limpiador y Desengrasante Servicio Pesado a Todos los Efectos

Manejo seguro

Evite el contacto con los ojos.

EN CASO DE CONTACTO CON LOS OJOS: Aclare cuidadosamente con agua durante varios minutos. Quite las lentes de contacto, si lleva y resulta fácil. Sigue aclarando. Si persiste la irritación ocular: Consulte a un médico.

Equipo de protección personal: Lleve guantes de protección. Lleve gafas de protección.


Disposición del producto no usado: El producto no usado o sus soluciones pueden ser vertidos en el desagüe. Nunca vierta el producto no usado o sus soluciones en un desagüe exterior.

La dilución impropia o el empleo impropio de este producto pueden resultar en una irritación de la piel y de los ojos, en daño a superficies y en una limpieza insatisfactoria.

Reciclaje de paquete: Paquetes vacíos deberán ser enjuagados con agua fría y luego colocados para reciclar donde aceptado.



INTRUCCIONES



Vacíe el contenido de un paquete de GS Extra-Strength Cleaner Concentrate en agua fría (consulte las tasas de dilución a continuación). Limpie con un paño húmedo. Vacíe y enjuague la botella antes de volver a llenarla.

Diluciones

#2308534, #2385300, #2313743, #2313767 - Mezcle cada paquete con 1 cuarto de galón de agua fría para la limpieza de todos los fines de pulverización y limpieza. Mezcle con 1 galón de agua fría para fregar o 2 galones para trapear húmedo.

#2384200, #2384204 - Mezcle con 2 galones de agua fría para fregar o 4 galones para trapear húmedo.

#2384309 - Mezcle cada paquete con 4 galones de agua fría para fregar o 8 galones para trapear húmedo.



This product meets Green Seal™ Standard GS-37 based on effective performance, concentrated volume, minimized/recycled packaging and protective limits on: VOCs and human & environmental toxicity. GreenSeal.org.

The U.S. EPA's Safer Choice Program helps consumers, businesses, and institutional buyers identify cleaning and other products that perform well and are safer for people and the environment.

