1. Identification

Product Identity: HD HI-Foam

General Purpose water-based degreaser Recommended Use:

Producer / Distributor

Multi-Clean 600 Cardigan Road Shoreview, MN 55126

651-481-1900 **Telephone Number for Information: Emergency Telephone Number:** 800-255-3924




Acute Aquatic Toxicity Category 2

2 **Hazard Identification**

Classification:

Physical Class Environment Class Health Class

Skin Corrosion Category 1 Serious Eye Damage Category 1 Reproductive Toxicity Category 2





Symbols





Signal Word Danger

Hazard Statements:

Causes severe skin burns and eve damage.

Suspected of damaging fertility or the unborn child.

May cause damage to kidneys through prolonged or repeated exposure.

Precautionary Statements:

Do not handle until all safety precautions have been read and understood.

Wear protective gloves/protective clothing/eye protection/face protection.

Do not breathe dust/fume/gas/mist/vapors/spray.

Wash hands thoroughly after handling.

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

IF SWALLOWED: Rinse mouth. Do NOT induce vomiting.

IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water.

Wash contaminated clothing before reuse.

IF INHALED: Remove person to fresh air and keep comfortable for breathing. Immediately call a doctor.

If exposed or concerned: Get medical attention.

Store locked up.

Dispose of contents in accordance with local regulations.

Composition/Information on Ingredients Percent by Ingredient **CAS Number** Weight Potassium Hydroxide 1310-58-3 1 - 5 Lauramide Oxide 1643-20-5 1 - 5 Tetra-Sodium Salt EDTA 64-02-8 1 - 5 Water 7732-18-5 60 - 100

First-Aid Measures:

Ingestion: If Swallowed: Do not induce vomiting. Drink water in large amounts and call a physician immediately. Never give anything by

mouth to an unconscious person.

Eye Contact: Flush eyes with running water for at least 15 minutes. If irritation persists, obtain medical attention.

Skin Contact: Flush thoroughly with cool water. Remove and wash contaminated clothing before reuse.

Inhalation: Move to fresh air.

5. Fire Fighting Measures:

Suitable Extinguishing Media: Not Applicable Not Applicable **Special Fire Fighting Procedures: Unusual Fire and Explosion Hazards** Not Applicable

Accidental Release Measures:

Dike and contain spill with inert material (sand, earth, etc.). Collect spill with a mop, absorbent material (example: floor-dry) or vacuum. Thoroughly rinse affected area with water.

7. Handling and Storage:

Handling: Keep from freezing. Keep out of reach of children.

Storage: Normal care for storage.

8. Exposure Controls / Personal Protection:

 Exposure Limits
 Ingredients
 CAS Number
 Osha PEL
 ACGIH TLV

 Potassium Hydroxide
 1310-58-3
 2 mg/M3
 2 mg/M3

Exposure Controls

Engineering Controls: Normal good ventilation is sufficient

Personal Protective Equipment:

Eye Protection: Approved Safety Goggles or Glasses **Skin Protection:** Chemical Resistant Rubber Gloves

Respiratory Protection: Not required, Avoid breathing spray mist

9. Physical and Chemical Properties:

Physical State: Liquid pH: > 13

Appearance: Clear Specific Gravity (H2O = 1): 1.04

Odor:MildFlammability:NoneSolubility:CompleteFlash Point:None

Evaporation Rate: NA **Boiling Point:** > 212° F (100°C)

Vapor Pressure (MM HG): NA %volatile: 60 - 100%

Vapor Density (Air = 1): NA

10. Stability and Reactivity:

Chemical Stability: Stable

Possibility of Hazardous Reactions: None are known Incompatability (Materials to Avoid): None are known Hazardous Decomposition or By-products: None Hazardous Polymerization: Will not Occur

Hazardous Polymerization: Will not Occu
Conditions to Avoid: None are known

11. Toxicological Information:

Signs and Symptoms of Overexposure: Eye Contact: Possible burning, tearing, redness and corneal damage. Skin Contact:

Possible slippery feeling, redness, swelling and burns. Symptoms may be delayed.

Acute Effects:

Eye Contact: Severe Eye damage can result from direct contact.

Skin Contact: Causes severe skin burns

Inhalation: None Known

Ingestion: May be harmful if swallowed

Target Organ Effects: Kidneys and Suspected of damaging fertility or the unborn child. **Chronic Effects:** May cause damage to kidneys through prolonged or repeated exposure.

Acute Toxicity Values:

Oral LD ₅₀ > 5000 mg/kg **Dermal LD** ₅₀ > 5000 mg/kg

Inhalation (Vapor) LC 50 Vapors Considered Non-T

12. Ecological Information:

Persistence and Degradability: Not Available Bio Accumulative Potential: Not Available

Mobility in Soil: Not Available

Aquatic Toxicity: Toxic to Aquatic Life

13. Disposal Considerations:

Material that cannot be used during normal use should be disposed of in accordance with all applicable local, state and federal regulations. Waste from normal cleaning procedures may be neutralized and disposed of in a sanitary sewer depending on the materials and/or contaminants being cleaned as well as local, state and federal sewer regulations.

14. Transportation Information:

UN Number: UN3266

Shipping Name: Corrosive, Liquid, Basic, Inorganic, N.O.S. (Potassium Hydroxide)

Transport Hazard Class: 8

Packing Group: II
Marine Pollutant: NO

15. Regulatory Information:

TSCA Status: All ingredients listed

Clean Water Act: Potassium Hydroxide(1310-58-3) is listed in the Clean Water Act as a Hazardous Substance.

Clean Air Act: None of the chemicals in this product are listed under the CAA CERCLA Reportable Quantity: Potassium Hydroxide (1310-58-3), > 1000 lbs.

SARA Title III Information:

Section 302 Extremely Hazardous Chemicals: None Listed Section 311 / 312 Hazard Category: Immediate Health

Section 313 Toxic Chemicals: None Listed

State Regulations: None

International Regulations: WHMIS Controlled Product Hazard Class: E

16. Other Information:

Prepared By: Eric Scholl

Telephone Number: 651-481-1900

Revision Date: 7/21/2014 **Supersedes:** 6/7/2013

This SDS applies to the following Part

Numbers

910923 910927 The information contained herein is based on data considered accurate; however no warranty is expressed or implied regarding the accuracy of this data or the results to be obtained from the use thereof. The company assumes no responsibility for personal injury or property damage to vendees, users, or third parties caused by the material. Such vendees or users assume all risks associated with the use of the material.



Health	2
Flammability	0
Physical hazards	0