

**1. Identification****Product Identity:** Ultra Stripper**Recommended Use:** Water-based floor finish stripper**Producer / Distributor**

Multi-Clean  
600 Cardigan Road  
Shoreview, MN 55126

**Telephone Number for Information:** 651-481-1900**Emergency Telephone Number:** 800-255-3924**2. Hazard Identification****Classification:****Health Class**

Acute Toxicity Category 4  
Skin Corrosion Category 1  
Serious Eye Damage Category 1  
Skin Sensitizer  
Reproductive Toxicity Category 1  
Specific Target Organ Toxicity - Single Exposure Category 2  
Specific Target Organ Toxicity - Repeated Exposure Category 1

**Physical Class****Environment Class****Label****Symbols****Signal Word** Danger**Hazard Statements:**

Harmful if swallowed.  
Causes severe skin burns and eye damage.  
May cause an allergic skin reaction.  
May damage fertility or the unborn child.  
May cause damage to central nervous system, respiratory tract and/or lungs through prolonged or repeated exposure.  
Causes damage to kidneys, liver, and through prolonged or repeated exposure.

**Precautionary Statements:**

Do not handle until all safety precautions have been read and understood.  
Wear protective gloves/protective clothing/eye protection/face protection.  
Avoid breathing dust/fume/gas/mist/vapors/spray.  
Contaminated work clothing should not be allowed out of the workplace.  
Wash hands thoroughly after handling.  
Do not eat, drink or smoke when using this product.  
IF SWALLOWED: Rinse mouth. Do NOT induce vomiting. Call a doctor if you feel unwell.  
IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.  
IF ON SKIN (or hair): Take off immediately all contaminated clothing. Wash skin with plenty of water.  
Wash contaminated clothing before reuse.  
If skin irritation or rash occurs: Get medical attention  
IF INHALED: Remove person to fresh air and keep comfortable for breathing. Immediately call a doctor.  
If exposed or concerned: Get medical attention.  
Store locked up.  
Dispose of contents in accordance with local regulations.

**3. Composition/Information on Ingredients**

Ingredient	CAS Number	Percent by Weight
Benzyl Alcohol	100-51-6	20 - 25
Dipropylene Glycol Monomethyl Ether	34590-94-8	5 - 10
Tall Oil Fatty Acid	61790-12-3	5 - 10
Ethanolamine	141-43-5	3 - 7
Fragrance	Proprietary	< 1
Water	7732-18-5	40 - 70

**4. First-Aid Measures:**

**Ingestion:** If Swallowed: Do not induce vomiting. If person can swallow, give several glasses of water. Obtain immediate medical attention.

**Eye Contact:** Immediately flush eyes with running water for at least 15 minutes. Obtain immediate medical attention.

**Skin Contact:** Flush thoroughly with cool water. Remove and wash contaminated clothing before reuse.

**Inhalation:** Remove to fresh air. If irritation persists, obtain medical attention.

#### 5. Fire Fighting Measures:

**Suitable Extinguishing Media:** Not Applicable  
**Special Fire Fighting Procedures:** Not Applicable  
**Unusual Fire and Explosion Hazards:** Not Applicable

#### 6. Accidental Release Measures:

Dike and contain spill with inert material (sand, earth, etc.). Collect spill with a mop, absorbent material (example: floor-dry) or vacuum. Thoroughly rinse affected area with water.

#### 7. Handling and Storage:

**Handling:** Keep from freezing. Keep out of reach of children.  
**Storage:** Normal care for storage.

#### 8. Exposure Controls / Personal Protection:

##### Exposure Limits

Ingredients	CAS Number	Osha PEL	ACGIH TLV
Benzyl Alcohol	100-51-6	10 ppm	10 ppm
Dipropylene Glycol Monomethyl Ether			
Ethanolamine			

##### Exposure Controls

**Engineering Controls:** Ventilate to maintain vapor levels below exposure limits.

##### Personal Protective Equipment:

**Eye Protection:** Approved Safety Goggles or Glasses

**Skin Protection:** Chemical Resistant Rubber Gloves

**Respiratory Protection:** Not required where ventilation is sufficient to maintain vapor level below listed TLV

#### 9. Physical and Chemical Properties:

<b>Physical State:</b> Liquid	<b>pH:</b> 10 - 11
<b>Appearance:</b> Amber	<b>Specific Gravity (H<sub>2</sub>O = 1):</b> 1.01
<b>Odor:</b> Fresh Citrus	<b>Flammability:</b> None
<b>Solubility:</b> Complete	<b>Flash Point:</b> None
<b>Evaporation Rate:</b> NA	<b>Boiling Point:</b> > 212° F (100°C)
<b>Vapor Pressure (MM HG):</b> NA	<b>%volatile:</b> 75 - 100%
<b>Vapor Density (Air = 1):</b> > 1	

#### 10. Stability and Reactivity:

**Chemical Stability:** Stable  
**Possibility of Hazardous Reactions:** None are known  
**Incompatibility (Materials to Avoid):** Strong Oxidizers, Strong Acids  
**Hazardous Decomposition or By-products:** None  
**Hazardous Polymerization:** Will not Occur  
**Conditions to Avoid:** None are known

#### 11. Toxicological Information:

**Signs and Symptoms of Overexposure:** May irritate Mucous Membranes, Eyes may show signs of burning, tearing, and redness

##### Acute Effects:

**Eye Contact:** Severe Eye damage can result from direct contact.

**Skin Contact:** Causes severe skin burns

**Inhalation:** May be harmful with overexposure

**Ingestion:** Harmful if swallowed

**Target Organ Effects:** Central nervous system, Liver, Kidneys, Respiratory tract, Lungs and May damage fertility or the unborn child.

**Chronic Effects:** May cause damage to central nervous system, respiratory tract and/or lungs and causes damage to kidneys, liver, and central nervous system through prolonged or repeated exposure.

##### Acute Toxicity Values:

**Oral LD<sub>50</sub>** 300 - 2000 mg/kg  
**Dermal LD<sub>50</sub>** 1000 - 2000 mg/kg  
**Inhalation (Vapor) LC<sub>50</sub>** 10 - 20 mg/l

**12. Ecological Information:**

**Persistence and Degradability:** Not Available  
**Bio Accumulative Potential:** Not Available  
**Mobility in Soil:** Not Available  
**Aquatic Toxicity:** Not Available

**13. Disposal Considerations:**

Material that cannot be used during normal use should be disposed of in accordance with all applicable local, state and federal regulations. Waste from normal cleaning procedures may be disposed of in a sanitary sewer depending on the materials and/or contaminants being cleaned as well as local, state and federal sewer regulations.

**14. Transportation Information:**

**UN Number:** None  
**Shipping Name:** Cleaning Compound, Liquid  
**Transport Hazard Class:** None  
**Packing Group:** None  
**Marine Pollutant:** NO


**15. Regulatory Information:**

**TSCA Status:** All ingredients listed  
**Clean Water Act:** None of the chemicals in this product are listed under the CWA  
**Clean Air Act:** None of the chemicals in this product are listed under the CAA  
**CERCLA Reportable Quantity:** None  
**SARA Title III Information:**  
**Section 302 Extremely Hazardous Chemicals:** None Listed  
**Section 311 / 312 Hazard Category:** Immediate Health, Chronic Health  
**Section 313 Toxic Chemicals:** None Listed  
**State Regulations:** None  
**International Regulations:** WHMIS Controlled Product Hazard Class: D2B

**16. Other Information:**

**Prepared By:** Eric Scholl  
**Telephone Number:** 651-481-1900  
**Revision Date:** 11/28/2018  
**Supersedes:** 2/7/2018  
**This SDS applies to the following Part Numbers**  
 903983  
 903985  
 903987

The information contained herein is based on data considered accurate; however no warranty is expressed or implied regarding the accuracy of this data or the results to be obtained from the use thereof. The company assumes no responsibility for personal injury or property damage to vendees, users, or third parties caused by the material. Such vendees or users assume all risks associated with the use of the material.



<b>Health</b>	2
<b>Flammability</b>	0
<b>Physical hazards</b>	0