

	<h1>Safety Data Sheet</h1>	<p>24 Hour Emergency Phone Numbers Medical/Poison Control: In U.S.: Call 1-800-222-1222</p> <p>Outside U.S.: Call your local poison control center</p> <p>Transportation/National Response Center:</p> <p style="text-align: center;">1-800-535-5053 1-352-323-3500</p> <p>NOTE: The National Response Center emergency numbers to be used only in the event of chemical emergencies involving a spill, leak, fire, exposure or accident involving chemicals.</p>
---	----------------------------	---

IMPORTANT: Provide this information to employees, customers, and users of this product. Read this SDS before handling or disposing of this product. This product is covered by the OSHA Hazard Communication Standard and this document has been prepared in accordance with requirements of this standard. All abbreviated terms used in this SDS are further described in Section 16.

1. Identification

This Safety Data Sheet is available in American Spanish upon request.
 Los Datos de Seguridad pueden obtenerse en Espanol si lo requiere.

Product Name:	Dynagrip Heavy Duty Construction Adhesive	Revision Date:	12/12/2016
Product UPC Number:	070798275089, 07098275096, 070798275102	Supersedes Date:	New SDS
Product Use/Class:	Construction Adhesive	SDS No:	00070085001
Manufacturer:	DAP Products Inc. 2400 Boston Street Suite 200 Baltimore, MD 21224-4723 888-327-8477 (non - emergency matters)	Preparer:	Regulatory Department
Emergency Telephone:	1-800-535-5053, 1-352-323-3500, 1-800-222-1222		
Safety Data Sheet Coordinator:	MSDS@DAP.com		

2. Hazards Identification

EMERGENCY OVERVIEW: May cause eye, skin, nose, throat and respiratory tract irritation. Harmful if swallowed or absorbed through the skin.

GHS Classification

Not a hazardous substance or mixture.

Symbol(s) of Product

None

Signal Word

Not a hazardous substance or mixture.

Possible Hazards

28% of the mixture consists of ingredients of unknown acute toxicity

3. Composition/Information on Ingredients

<u>Chemical Name</u>	<u>CAS-No.</u>	<u>Wt. %</u>	<u>GHS Symbols</u>	<u>GHS Statements</u>
Calcium Carbonate	471-34-1	25-50	GHS07	H332
Magnesite	546-93-0	2.5-10	No Information	No Information
Potassium tripolyphosphate	13845-36-8	1.0-2.5	GHS06	H302-330

The text for GHS Hazard Statements shown above (if any) is given in the "Other information" Section.

4. First-aid Measures

FIRST AID - INHALATION: If inhaled, remove to fresh air. If breathing is difficult, leave the area to obtain fresh air. If continued breathing difficulty is experienced, get medical attention immediately.

FIRST AID - SKIN CONTACT: Remove and wash contaminated clothing. Wash off immediately with soap and plenty of water for at least 15 minutes. Get medical aid if symptoms persist.

FIRST AID - EYE CONTACT: In case of contact, immediately flush eyes with large quantities of water for at least 15 minutes until irritation subsides. Get medical attention immediately.

FIRST AID - INGESTION: If swallowed, DO NOT INDUCE VOMITING. Get medical attention immediately.

5. Fire-fighting Measures

UNUSUAL FIRE AND EXPLOSION HAZARDS: No Information

SPECIAL FIREFIGHTING PROCEDURES: Wear self-contained breathing apparatus pressure-demand (NIOSH approved or equivalent) and full protective gear. Use water spray to cool exposed surfaces.

EXTINGUISHING MEDIA: Alcohol Foam, Carbon Dioxide, Dry Chemical, Foam

6. Accidental Release Measures

ENVIRONMENTAL MEASURES: No Information

STEPS TO BE TAKEN IF MATERIAL IS RELEASED OR SPILLED: Contain spilled material and remove with inert absorbent. Dispose of contaminated absorbent, container and unused contents in accordance with local, state and federal regulations. Scrape up dried material and place into containers. Use personal protective equipment as necessary. In case of spillage, absorb with inert material and dispose of in accordance with applicable regulations.

7. Handling and Storage

HANDLING: KEEP OUT OF REACH OF CHILDREN! DO NOT TAKE INTERNALLY. Avoid breathing vapor and contact with eyes, skin and clothing. Use only with adequate ventilation. Open all windows and doors or use other means to ensure cross-ventilation and fresh air entry during application and drying. Odor is not an adequate warning for hazardous conditions. Wash thoroughly after handling.

STORAGE: Avoid excessive heat and freezing. Do not store at temperatures above 120 degrees F. Store away from caustics and oxidizers.

8. Exposure Controls/Personal Protection

Ingredients with Occupational Exposure Limits

<u>Chemical Name</u>	<u>ACGIH TLV-TWA</u>	<u>ACGIH-TLV STEL</u>	<u>OSHA PEL-TWA</u>	<u>OSHA PEL-CEILING</u>
Calcium Carbonate	N.E.	N.E.	N.E.	N.E.
Magnesite	N.E.	N.E.	N.E.	N.E.
Potassium tripolyphosphate	N.E.	N.E.	N.E.	N.E.

Further Advice: MEL = Maximum Exposure Limit OES = Occupational Exposure Standard SUP = Supplier's Recommendation
Sk = Skin Sensitizer N.E. = Not Established

Personal Protection



RESPIRATORY PROTECTION: No personal respiratory protective equipment normally required. In case of insufficient ventilation, wear suitable respiratory equipment.



SKIN PROTECTION: Rubber gloves.



EYE PROTECTION: Goggles or safety glasses with side shields.



OTHER PROTECTIVE EQUIPMENT: Not required under normal use.



HYGIENIC PRACTICES: Wash hands before breaks and at the end of workday. Remove and wash contaminated clothing before re-use.

9. Physical and Chemical Properties

Appearance:	White to Off-White	Physical State:	Paste
Odor:	Slight	Odor Threshold:	Not Established
Density, g/cm³:	1.34 - 1.34	pH:	Between 7.0 and 12.0
Freeze Point, °C:	Not Established	Viscosity (mPa.s):	Not Established
Solubility in Water:	No Information	Partition Coeff., n-octanol/water:	Not Established
Decomposition Temperature, °C:	Not Established	Explosive Limits, %:	N.I. - N.I.
Boiling Range, °C:	N.I. - N.I.	Auto-Ignition Temperature, °C	Not Established
Minimum Flash Point, °C:	93.3	Vapor Pressure, mmHg:	Not Established
Evaporation Rate:	Slower Than n-Butyl Acetate	Flash Method:	Seta Closed Cup
Vapor Density:	Heavier Than Air	Flammability:	Non-Flammable
Combustibility:	Does not support combustion		

(See "Other information" Section for abbreviation legend)

(If product is an aerosol, the flash point stated above is that of the propellant.)

10. Stability and Reactivity

STABILITY: Stable under recommended storage conditions.

CONDITIONS TO AVOID: Excessive heat and freezing.

INCOMPATIBILITY: Incompatible with strong bases and oxidizing agents.

HAZARDOUS DECOMPOSITION PRODUCTS: Normal decomposition products, i.e., CO_x, NO_x.

11. Toxicological Information

EFFECT OF OVEREXPOSURE - INHALATION: May be harmful if inhaled. Inhalation may cause irritation to the respiratory tract (nose, mouth, mucous membranes).

EFFECT OF OVEREXPOSURE - SKIN CONTACT: Prolonged or repeated contact with skin may cause mild irritation.

EFFECT OF OVEREXPOSURE - EYE CONTACT: May cause eye irritation of susceptible persons.

EFFECT OF OVEREXPOSURE - INGESTION: Harmful if swallowed.

CARCINOGENICITY: No Information

EFFECT OF OVEREXPOSURE - CHRONIC HAZARDS: Prolonged and repeated skin contact may cause irritation and possibly dermatitis.

PRIMARY ROUTE(S) OF ENTRY: Eye Contact, Inhalation, Skin Contact

Acute Toxicity Values

The acute effects of this product have not been tested. Data on individual components are tabulated below

<u>CAS-No.</u>	<u>Chemical Name</u>	<u>Oral LD50</u>	<u>Dermal LD50</u>	<u>Vapor LC50</u>
471-34-1	Calcium Carbonate	6450 mg/kg Rat	>2000 mg/kg Rat	>20 mg/L
546-93-0	Magnesite	>2000 mg/kg Rat	>2000 mg/kg	>20 mg/L
13845-36-8	Potassium triphosphate	2000 mg/kg Rat	4640 mg/kg Rabbit	> 0.39 mg/L Rat

N.I. = No Information

12. Ecological Information

ECOLOGICAL INFORMATION: Ecological injuries are not known or expected under normal use.

13. Disposal Information

DISPOSAL INFORMATION: This product does not meet the definition of a hazardous waste according to U.S. EPA Hazardous Waste Management Regulation, 40 CFR Section 261. Dispose as hazardous waste according to all local, state, federal and provincial regulations. State and Local regulations/restrictions are complex and may differ from Federal regulations. Responsibility for proper waste disposal is with the owner of the waste.

14. Transport Information

SPECIAL TRANSPORT PRECAUTIONS: No Information

DOT UN/NA Number:	N.A.
DOT Proper Shipping Name:	Not Regulated.
DOT Technical Name:	N.A.
DOT Hazard Class:	N.A.
Hazard SubClass:	N.A.
Packing Group:	N.A.

15. Regulatory Information

U.S. Federal Regulations:

CERCLA - SARA Hazard Category

This product has been reviewed according to the EPA 'Hazard Categories' promulgated under Sections 311 and 312 of the Superfund Amendment and Reauthorization Act of 1986 (SARA Title III) and is considered, under applicable definitions, to meet the following categories:

Acute Health Hazard, Chronic Health Hazard

SARA SECTION 313:

This product contains the following substances subject to the reporting requirements of Section 313 of Title III of the Superfund Amendment and Reauthorization Act of 1986 and 40 CFR part 372:

No Sara 313 components exist in this product.

TOXIC SUBSTANCES CONTROL ACT:

All ingredients in this product are either on TSCA inventory list, or otherwise exempt.

This product contains the following chemical substances subject to the reporting requirements of TSCA 12(B) if exported from the United States:

No TSCA 12(b) components exist in this product.

CALIFORNIA PROPOSITION 65 CARCINOGENS AND REPRODUCTIVE TOXINS

CALIFORNIA PROPOSITION 65: WARNING: This product contains chemicals known to the State of California to cause cancer, birth defects or other reproductive harm.

