



# 95% AFUE SINGLE STAGE GAS FURNACE

MGM95S\*XA

MGD95S\*XA





A compact, easily maintained, affordable and efficient gas heating solution.

- Upflow / Horizontal & Downflow configurations
- 10-Year Parts / 20-Year Heat Exchanger Limited Warranty ‡

‡Warranty provides for a total of 10 years of limited warranty coverage (Standard 5-year limited parts warranty plus an additional 5-year limited extended parts warranty; 15-year for heat exchanger). Warranty must be registered online within 60 days of installation to qualify for extended coverage. Unregistered equipment defaults to 5-year coverage.

All units AHRI & CSA Certified

## FEATURES & BENEFITS

-  Compact 33" height and standardized widths for easy coil fit
-  Aluminized no-weld steel primary heat exchanger  
AL 29-4C stainless steel secondary heat exchanger
-  MGM95S\*XA Upflow / Horizontal & MGD95S\*XA Downflow configurations
-  Self diagnostics saves last 5 fault codes regardless of power interruption
-  Optional LP & High Altitude Kits
  - Multi-speed PSC blower motor (easily removable slide out)
  - Control features electronic air cleaner and humidifier terminals
  - Single stage gas valve
  - Designed certified for direct and non direct applications
  - Left or right utility connections, removable floor base for bottom return air, zero step horizontal conversion

