

1. Identification**Product Identity:** 80 Fury Degreaser**Recommended Use:** Water-Based Cleaner & Degreaser**Producer / Distributor**Multi-Clean
600 Cardigan Road
Shoreview, MN 55126**Telephone Number for Information:** 651-481-1900**Emergency Telephone Number:** 800-255-3924

310

**2. Hazard Identification****Classification:****Health Class**Mild Skin Irritation Category 3
Eye Irritation Category 2**Physical Class****Environment Class****Label****Symbols****Signal Word** Warning**Hazard Statements:**Causes mild skin irritation.
Causes eye irritation.**Precautionary Statements:**Wash hands thoroughly after handling.
If skin irritation occurs: Get medical attention.
IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
If eye irritation persists: Get medical attention.**3. Composition/Information on Ingredients**

Ingredient	CAS Number	Percent by Weight
Sodium Gluconate	527-07-1	1 - 5
Sodium Carbonate	497-19-8	1 - 5
Alcohols, alkoxylated	Proprietary	1 - 10
Water	7732-18-5	60 - 100

4. First-Aid Measures:**Ingestion:** If swallowed: If the person can swallow, give several glasses of water. Obtain medical attention**Eye Contact:** Flush eyes with running water for at least 15 minutes. If irritation persists, obtain medical attention**Skin Contact:** Flush thoroughly with cool water. Remove and wash contaminated clothing before reuse.**Inhalation:** If ill effects occur from breathing vapors, remove to fresh air and obtain medical attention.**5. Fire Fighting Measures:****Suitable Extinguishing Media:** Not Applicable**Special Fire Fighting Procedures:** Not Applicable**Unusual Fire and Explosion Hazards** None are known**6. Accidental Release Measures:**Dike and contain spill with inert material (sand, earth, etc.). Collect spill with a mop, absorbent material (example: floor-dry) or vacuum.
Thoroughly rinse affected area with water.**7. Handling and Storage:****Handling:** Keep from freezing. Keep out of reach of children.**Storage:** Normal care for storage.

8. Exposure Controls / Personal Protection:**Exposure Limits****Ingredients**

None Listed

CAS Number

XXXX

Osha PEL

XXX

ACGIH TLV

XXX

Exposure Controls**Engineering Controls:** Normal good ventilation is sufficient**Personal Protective Equipment:****Eye Protection:** Approved Safety Goggles or Glasses**Skin Protection:** Chemical Resistant Rubber Gloves**Respiratory Protection:** Not Required**9. Physical and Chemical Properties:****Physical State:** Liquid**pH:** 10.5 - 11.5**Appearance:** Red**Specific Gravity (H₂O = 1):** 1.04**Odor:** None**Flammability:** Not flammable**Solubility:** Complete**Flash Point:** >199.9°F (>93.3°C)**Evaporation Rate:** NA**Boiling Point:** > 212° F (100°C)**Vapor Pressure (MM HG):** NA**%volatile:** > 75%**Vapor Density (Air = 1):** NA**10. Stability and Reactivity:****Chemical Stability:** Stable**Possibility of Hazardous Reactions:** None are known**Incompatibility (Materials to Avoid):** None are known**Hazardous Decomposition or By-products:** None**Hazardous Polymerization:** Will not Occur**Conditions to Avoid:** None are known**11. Toxicological Information:****Signs and Symptoms of Overexposure:** Causes irritation on direct contact**Acute Effects:****Eye Contact:** Causes irritation on contact**Skin Contact:** Causes mild irritation on prolonged or repeated contact**Inhalation:** May be harmful with overexposure**Ingestion:** May be harmful if swallowed**Target Organ Effects:** None known**Chronic Effects:** None known**Acute Toxicity Values:****Oral LD₅₀** > 5000 mg/kg**Dermal LD₅₀** > 5000 mg/kg**Inhalation (Vapor) LC₅₀** > 50 mg/l**12. Ecological Information:****Persistence and Degradability:** Not Available**Bio Accumulative Potential:** Not Available**Mobility in Soil:** Not Available**Aquatic Toxicity:** Not Available**13. Disposal Considerations:**

Material that cannot be used during normal use should be disposed of in accordance with all applicable local, state and federal regulations. Waste from normal cleaning procedures may be disposed of in a sanitary sewer depending on the materials and/or contaminants being cleaned as well as local, state and federal sewer regulations.

14. Transportation Information:**UN Number:** None**Shipping Name:** Cleaning Compound, Liquid**Transport Hazard Class:** None**Packing Group:** None**Marine Pollutant:** NO

15. Regulatory Information:

TSCA Status: All ingredients listed

Clean Water Act: None of the chemicals in this product are listed under the CWA

Clean Air Act: None of the chemicals in this product are listed under the CAA

CERCLA Reportable Quantity: None

SARA Title III Information:

Section 302 Extremely Hazardous Chemicals: None Listed

Section 311 / 312 Hazard Category: None

Section 313 Toxic Chemicals None Listed

State Regulations: None

International Regulations: None

California Cleaning Product Right to Know Act of 2017 (SB 258)

Raw Material	CAS No	Function	List
Water	7732-18-5	Diluent	Not Applicable
Alcohol Ethoxylate	68551-12-2	Detergent	Not Applicable
Sodium Gluconate	527-07-1	Chelator	Not Applicable
Sodium Carbonate	497-19-8	Chelator	Not Applicable
Sodium Xylenesulfonate	1300-72-7	Processing Aid	Not Applicable
ethylenediamine tetraacetate	64-02-8	Acid	Not Applicable
Citric Acid	77-92-9	Buffer	Not Applicable
Colorant	Withheld	Dye	Not Applicable

16. Other Information:

Prepared By: Jeremy Waldner

Telephone Number: 651-481-1900

Revision Date: 1/1/2020

Supersedes: 7/24/2019

This SDS applies to the following Part Numbers

908682

The information contained herein is based on data considered accurate; however no warranty is expressed or implied regarding the accuracy of this data or the results to be obtained from the use thereof. The company assumes no responsibility for personal injury or property damage to vendees, users, or third parties caused by the material. Such vendees or users assume all risks associated with the use of the material.



Health	1
Flammability	0
Physical hazards	0