

# Safety Data Sheet

24 Hour Emergency Phone Numbers Medical/Poison Control:

In U.S.: Call 1-800-222-1222

Outside U.S.: Call your local poison control center

Transportation/National Response Center:

Affairs

1-800-535-5053 1-352-323-3500

NOTE: The National ResponseCenter emergency numbers to be used only in the event of chemical emergencies involving a spill, leak, fire, exposure or accident involving chemicals.

IMPORTANT: Provide this information to employees, customers, and users of this product. Read this SDS before handling or disposing of this product. This product is covered by the OSHA Hazard Communication Standard and this document has been prepared in accordance with requirements of this standard. All abbreviated terms used in this SDS are further described in Section 16.

## 1. Identification

**Product UPC Number:** 

This Safety Data Sheet is available in American Spanish upon request. Los Datos de Serguridad pueden obtenerse en Espanol si lo riquiere.

Supercedes Date:

3/15/2018 **Product Name:** DAP RapidFuse Adhesive **Revision Date:** 

070798001558, 070798001565, 8/8/2016

070798001572, 070798001589,

070798001701, 070798001732

00030406004 **Product Use/Class:** Adhesive SDS No:

DAP Products Inc. Regulatory and Environmental Manufactured For Preparer:

2400 Boston Street Suite 200 Baltimore, MD 21224-4723

888-327-8477 (non - emergency matters)

SDS Coordinator: MSDS@dap.com

Emergency Telephone: 1-800-535-5053,

1-352-323-3500, 1-800-222-1222

## 2. Hazards Identification

EMERGENCY OVERVIEW: WARNING!Combustible liquid and vapor. Keep container closed and away from heat, sparks, and open flame. Store away from caustics and oxidizers. Cyanoacrylate. Danger. Bonds skin and eyes in seconds. Keep out of the reach of children. May cause skin irritation.

#### **GHS Classification**

Eye Irrit. 2, Skin Irrit. 2, STOT SE 3 RTI

## Symbol(s) of Product



#### Signal Word

Warning

#### Possible Hazards

6% of the mixture consists of ingredients of unknown acute toxicity

#### **GHS HAZARD STATEMENTS**

Skin Irritation, category 2 H315 Causes skin irritation.

Eye Irritation, category 2 H319 Causes serious eye irritation.

STOT, single exposure, category 3, RTI H335 May cause respiratory irritation.

#### **GHS LABEL PRECAUTIONARY STATEMENTS**

P261 Avoid breathing dust/fume/gas/mist/vapours/spray.

P264 Wash thoroughly after handling.

P271 Use only outdoors or in a well-ventilated area.

P280 Wear protective gloves/protective clothing/eye protection/face protection.

P302+P352 IF ON SKIN: Wash with plenty of soap and water.

P304+P340 IF INHALED: Remove person to fresh air and keep comfortable for breathing.

P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if

present and easy to do. Continue rinsing.

P312 Call a POISON CENTER or doctor/physician if you feel unwell.

P321 Specific treatment (see ... on this label).

P332+P313 If skin irritation occurs: Get medical advice/attention.
P337+P313 If eye irritation persists: Get medical advice/attention.

P362 Take off contaminated clothing.

P403+P233 Store in a well-ventilated place. Keep container tightly closed.

P405 Store locked up.

P501 Dispose of contents/container to ...

# 3. Composition/Information on Ingredients

 Chemical Name
 CAS-No.
 Wt. %
 GHS Symbols
 GHS Statements

 Ethyl cyanoacrylate
 7085-85-0
 75-100
 GHS07
 H312-315-319-335

 Dimethyl sebacate
 106-79-6
 2.5-10
 GHS07
 H302

Fumed silica 68909-20-6 1.0-2.5 No Information No Information

The text for GHS Hazard Statements shown above (if any) is given in the "Other information" Section.

## 4. First-aid Measures

**FIRST AID - INHALATION:** If you experience difficulty in breathing, leave the area to obtain fresh air. If continued difficulty is experienced, get medical attention immediately.

**FIRST AID - SKIN CONTACT:** Do not pull bonded skin apart. Soak in warm soapy water. Gently peel apart using a blunt object such as spoon.

FIRST AID - EYE CONTACT: If the eye is bonded shut, apply warm water with a wet pad to release the eyelashes. Adhesive will bond to eye protein and will cause the eye to periodically shed tears. This will help debond the adhesive. Keep eye covered until debonding is complete. Do not force eye open. Solid particles of cyanoacrylate may be trapped behind the eyelids and cause abrasive damage. Seek medical attention.

**FIRST AID - INGESTION:** Make sure airways are clear. Adhesive will immediately polymerize in mouth and will be impossible to swallow. Saliva will slowly separate the adhesive from mouth.

## 5. Fire-fighting Measures

**UNUSUAL FIRE AND EXPLOSION HAZARDS:** Vapor from this material will readily ignite at temperatures above 150 degrees F if an ignition source is present. Vapors may form an explosive mixture with air at temperatures above 150 degrees F. Eliminate sources of

ignition: heat, electrical equipment, sparks and flames.

**SPECIAL FIREFIGHTING PROCEDURES:** Wear self-contained breathing apparatus pressure-demand (NIOSH approved or equivalent) and full protective gear. Use water spray to cool exposed surfaces.

EXTINGUISHING MEDIA: Carbon Dioxide, Dry Chemical, Water Fog

#### Accidental Release Measures

**ENVIRONMENTAL MEASURES:** No Information

STEPS TO BE TAKEN IF MATERIAL IS RELEASED OR SPILLED: Immediately eliminate sources of ignition. Contain spilled material and remove with inert absorbent. Dispose of contaminated absorbent, container and unused contents in accordance with local, state and federal regulations. Dike to prevent entering any sewer or waterway. Transfer liquid to a holding container. Read all product instructions before using. Personal protective equipment should include impervious gloves, protective eye wear, and suitable work clothes. In case of spillage, absorb with inert material and dispose of in accordance with applicable regulations. Use absorbent material or scrape up dried material and place in container.

# 7. Handling and Storage

HANDLING: KEEP OUT OF REACH OF CHILDREN!DO NOT TAKE INTERNALLY. Keep away from open flames, hot surfaces and sources of ignition. Provide adequate ventilation. Wear appropriate personal protection. Avoid contact with eyes, skin and clothing.

**STORAGE:** Store away from sources of ignition and heat. Do not store at temperatures above 120 degrees F. Store containers away from excessive heat and freezing. Store away from caustics and oxidizers. Keep containers tightly closed.

# 8. Exposure Controls/Personal Protection

Ingredients with Occupational Exposure Limits

Chemical Name	ACGIH TLV-TWA	ACGIH-TLV STEL	OSHA PEL-TWA	OSHA PEL-CEILING
Ethyl cyanoacrylate	0.2 ppm TWA	N.E.	N.E.	N.E.
Dimethyl sebacate	N.E.	N.E.	N.E.	N.E.
Fumed silica	N.E.	N.E.	N.E.	N.E.

Further Advice: MEL = Maximum Exposure Limit OES = Occupational Exposure Standard SUP = Supplier's Recommendation Sk = Skin Sensitizer N.E. = Not Established

#### **Personal Protection**



RESPIRATORY PROTECTION: No personal respiratory protective equipment normally required.



**SKIN PROTECTION:** Chemical-resistant gloves and chemical goggles should be used to prevent skin and eye contact. None Required.



EYE PROTECTION: Safety glasses with side-shields.



**OTHER PROTECTIVE EQUIPMENT:** Wear suitable gloves and eye/face protection. Not required under normal use.



**HYGIENIC PRACTICES:** Avoid breathing vapor. Avoid skin contact. Avoid eye contact. Wash contaminated clothing before re-use.

Auto-Ignition Temperature, °C

Vapor Pressure, mmHg:

Flash Method:

Flammability:

Not Established

Not Established

Seta Closed Cup

Combustible

# 9. Physical and Chemical Properties

Appearance: Clear Physical State: Liquid

Sharp Odor: Odor Threshold: Not Established pH: Density, g/cm3: 1.08 - 1.08 Not Established Freeze Point, °C: Not Established Viscosity (mPa.s): ca. 4000 cps Solubility in Water: No Information Partition Coeff., n-octanol/water: Not Established Decomposition Temperature, °C: Not Established Explosive Limits, %: N.I. - N.I.

Boiling Range, °C: N.I. - N.I. Minimum Flash Point, °C: 88

Evaporation Rate: Faster Than n-Butyl Acetate

Vapor Density: Heavier Than Air

Combustibility: Does not support combustion

(See "Other information" Section for abbreviation legend)

(If product is an aerosol, the flash point stated above is that of the propellant.)

# 10. Stability and Reactivity

STABILITY: Stable under normal conditions.

**CONDITIONS TO AVOID:** Protect from water. Keep away from open flames, hot surfaces and sources of ignition. Keep away from oxidizing agents, strongly alkaline and strongly acid materials in order to avoid exothermic reactions.

**INCOMPATIBILITY:** Water, alcohols, bases, cotton, wool, cellulosic materialsOpen flames, hot surfaces and sources of ignition. Keep away from strong oxidizing agents, heat and open flames. Strong bases.

HAZARDOUS DECOMPOSITION PRODUCTS: Carbon monoxide, carbon dioxide

# 11. Toxicological Information

**EFFECT OF OVEREXPOSURE - INHALATION:** Inhalation may cause irritation to the respiratory tract (nose, mouth, mucous membranes).

EFFECT OF OVEREXPOSURE - SKIN CONTACT: Immediate bonding of skin may result upon contact.

EFFECT OF OVEREXPOSURE - EYE CONTACT: Immediate bonding of eyelids may result upon contact.

EFFECT OF OVEREXPOSURE - INGESTION: Immediate bonding of mouth may result upon contact.

**CARCINOGENICITY:** No Information

EFFECT OF OVEREXPOSURE - CHRONIC HAZARDS: Chronic exposure may cause dermatitis.

PRIMARY ROUTE(S) OF ENTRY: Eye Contact, Inhalation, Skin Contact

#### **Acute Toxicity Values**

The acute effects of this product have not been tested. Data on individual components are tabulated below

<u>CAS-No.</u> 7085-85-0	<u>Chemical Name</u> Ethyl cyanoacrylate	Oral LD50 5000 mg/kg Rat	Dermal LD50 2000 mg/kg Rabbit	Vapor LC50 <21.1 mg/L Rat
106-79-6	Dimethyl sebacate	2000 mg/kg Rat	N.I.	N.I.
68909-20-6	Fumed silica	N.I.	N.I.	N.I.

N.I. = No Information

# 12. Ecological Information

ECOLOGICAL INFORMATION: Ecological injuries are not known or expected under normal use.

### 13. Disposal Information

DISPOSAL INFORMATION: This product does not meet the definition of a hazardous waste according to U.S. EPA Hazardous

Waste Management Regulation, 40 CFR Section 261. Dispose as hazardous waste according to all local, state, federal and provincial regulations. State and Local regulations/restrictions are complex and may differ from Federal regulations. Responsibility for proper waste disposal is with the owner of the waste.

# 14. Transport Information

SPECIAL TRANSPORT PRECAUTIONS: Not regulated for transport as packaged. Not regulated for transport in nonbulk containers (<= 450 liters (119 gallons). The U.S. Department of Transportation (DOT) classification above is ONLY when transported in bulk containers (> 450 liters, 119 gallons).

Not a dagerous good under Internation Air Transport (IATA). Not a dagerous good under Internation Maritime Transport (IMO).

DOT UN/NA Number: NA1993

DOT Proper Shipping Name: Combustible liquid, n.o.s. DOT Technical Name: (Ethyl cyanoacrylate)

DOT Hazard Class: Combustible

Hazard SubClass: N.A. Packing Group:

# 15. Regulatory Information

#### **SARA SECTION 313:**

This product contains the following substances subject to the reporting requirements of Section 313 of Title III of the Superfund Amendment and Reauthorization Act of 1986 and 40 CFR part 372:

No Sara 313 components exist in this product.

#### **TOXIC SUBSTANCES CONTROL ACT:**

All ingredients in this product are either on TSCA inventory list, or otherwise exempt.

This product contains the following chemical substances subject to the reporting requirements of TSCA 12(B) if exported from the United States:

No TSCA 12(b) components exist in this product.

## 16. Other Information

Revision Date: 3/15/2018 Supersedes Date: 8/8/2016

Reason for revision: Revision Description Changed

Substance and/or Product Properties Changed in Section(s):

01 - Product Information

08 - Exposure Controls/Personal Protection

11 - Toxicological Information15 - Regulatory Information16 - Other Information

Substance Regulatory CAS Number Changed Substance Hazardous Flag Changed Substance Hazard Threshold % Changed

Revision Statement(s) Changed

Datasheet produced by: Regulatory Department

**HMIS Ratings:** 

Health: 2 Flammability: 1 Reactivity: 0 Personal Protection: X

VOC Less Water Less Exempt Solvent, g/L: 5.0

VOC Material, g/L: 5

VOC as Defined by California Consumer Product Regulation, Wt/Wt%: 0.5

VOC Actual, Wt/Wt%: 0.5

H302 Harmful if swallowed.
H312 Harmful in contact with skin.
H315 Causes skin irritation.
H319 Causes serious eye irritation.
H335 May cause respiratory irritation.

#### Icons for GHS Pictograms shown in Section 3 describing each ingredient:

**GHS07** 



Legend: N.A. - Not Applicable, N.E. - Not Established, N.D. - Not Determined

DAP believes the data and statements contained herein are accurate as of the date hereof. They are offered in good faith as typical values and not as a product specification. NO WARRANTY OF MERCHANTABILITY, WARRANTY OF FITNESS FOR ANY PARTICULAR PURPOSE OR ANY OTHER WARRANTY, EXPRESS OR IMPLIED, IS MADE WITH REGARD TO THE INFORMATION HEREIN PROVIDED OR THE PRODUCT TO WHICH THE INFORMATION REFERS. Since this document is intended only as a guide to the appropriate use and precautionary handling of the referenced product by a properly trained person, it is therefore the responsibility of the user to (i) review the recommendations with due consideration for the specific context of the intended use and (ii) determine if they are appropriate.