















MISTRAL 202 DS LP is a versatile and lightweight industrial vacuum with an "endless" safe bagging system. It's a great solution for lead, asbestos, silica and other toxic dusts.



Features

- ✓ Compact, portable and constructed with powder coated steel
- ✓ 2 powerful bypass motors with independent cooling
- \checkmark LONGOPAC safe bagging system (65 ft / 20 m)
- ✓ Adjustable height to facilitate transport on vehicles
- ✓ DUSTOP reverse pulse cleaning system
- ✓ Large filter surface
- ✓ Tangential inlet with cyclone filter protector

Filtration

Primary Filter	Cartridge	
Surface Area	32 ft ² (3 m ²)	
Media Class (IEC 60335-2-69)	PTFE Coated Polyester - Class M	
Cleaning System	DUSTOP	
Air Load - ft/min (m/h)	6.6 (120)	

Optionals

- Certified HEPA Class H14 (99.995% @ 0.18 μm)
- Antistatic Filter (Class M)
- · Disposable Bags

- Partial or Full Stainless Steel Frame
- Remote Control
- Earth Grounding

- · Partial or Full Stainless Steel Frame
- More Power Sources Available By Request

MISTRAL 202 DS LP

Voltage	V - Hz	115 - 60 1~
Power	HP (kW)	1.5 (1.1)
Max Water Lift	inH2O (mmH2O)	90.1 (2289)
Max Airflow	CFM (m³/h)	211.9 (360)
Capacity	gal (L)	LONGOPAC
Dimensions	in (WxLxH)	20 x 19 x 49
Weight	lbs (kg)	77 (35)
Noise Level (EN ISO 3744)	dB(A)	76
Suction Inlet	in (mm)	2 (50)