



# SAFETY DATA SHEET

## 1. Identification

**Product identifier** Extreme Duty Food Grade Grease

**Other means of identification**

**Product code** SL35615, SL35616, SL35617, SL35618

**Recommended use** Lubricating grease

**Recommended restrictions** None known.

**Manufacturer/Importer/Supplier/Distributor information**

**Manufactured or sold by:**

**Company name** CRC Industries, Inc.

**Address** 885 Louis Dr.  
Warminster, PA 18974 US

**Telephone**

**General Information** 215-674-4300

**Technical Assistance** 800-521-3168

**Customer Service** 800-272-4620

**24-Hour Emergency (CHEMTREC)** 800-424-9300 (US)  
703-527-3887 (International)

**Website** www.crcindustries.com

## 2. Hazard(s) identification

**Physical hazards** Not classified.

**Health hazards** Serious eye damage/eye irritation Category 2A  
Sensitization, skin Category 1

**Environmental hazards** Not classified.

**OSHA defined hazards** Not classified.

**Label elements**



**Signal word** Warning

**Hazard statement** May cause an allergic skin reaction. Causes serious eye irritation.

**Precautionary statement**

**Prevention** Avoid breathing vapors. Contaminated work clothing must not be allowed out of the workplace. Wear protective gloves and eye/face protection. Wash thoroughly after handling.

**Response** If on skin: Wash with plenty of water. If skin irritation or rash occurs: Get medical attention. Wash contaminated clothing before reuse. If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical attention.

**Storage** Store away from incompatible materials.

**Disposal** Dispose of contents/container in accordance with local/regional/national regulations.

**Hazard(s) not otherwise classified (HNOC)** None known.

## 3. Composition/information on ingredients

### Mixtures

Chemical name	Common name and synonyms	CAS number	%
White mineral oil		8042-47-5	40 - 70

Chemical name	Common name and synonyms	CAS number	%
Benzene, mono-C10-13-alkyl derivs., fractionation bottoms, heavy ends, sulfonated, calcium salts		148520-84-7	10 - 30
Calcium dodecylbenzenesulphonate		26264-06-2	1 - 5
Diboron calcium tetraoxide		13701-64-9	1 - 5

Specific chemical identity and/or percentage of composition has been withheld as a trade secret.

#### 4. First-aid measures

<b>Inhalation</b>	Remove victim to fresh air and keep at rest in a position comfortable for breathing. If not breathing, give artificial respiration. If breathing is difficult, trained personnel should give oxygen. Get medical attention if symptoms occur.
<b>Skin contact</b>	Remove contaminated clothing immediately and wash skin with soap and water. In case of eczema or other skin disorders: Seek medical attention and take along these instructions. Wash contaminated clothing before reuse.
<b>Eye contact</b>	Rinse immediately with plenty of water, also under the eyelids. Remove contact lenses, if present and easy to do. Continue to rinse for at least 15 minutes. Get medical attention if irritation develops and persists.
<b>Ingestion</b>	Rinse mouth. Drink 1 or 2 glasses of water. Never give anything by mouth to a victim who is unconscious or is having convulsions. Do not induce vomiting without advice from poison control center. If vomiting occurs, keep head low so that stomach content doesn't get into the lungs. Get medical attention if symptoms occur. If ingestion of a large amount does occur, call a poison control center immediately.
<b>Most important symptoms/effects, acute and delayed</b>	Rash. Severe eye irritation. Symptoms may include stinging, tearing, redness, swelling, and blurred vision. Skin irritation. May cause an allergic skin reaction. Dermatitis.
<b>Indication of immediate medical attention and special treatment needed</b>	Provide general supportive measures and treat symptomatically. Keep victim under observation. Symptoms may be delayed.
<b>General information</b>	Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves. Wash contaminated clothing before reuse.

#### 5. Fire-fighting measures

<b>Suitable extinguishing media</b>	Use fire-extinguishing media appropriate for surrounding materials.
<b>Unsuitable extinguishing media</b>	None known.
<b>Specific hazards arising from the chemical</b>	During fire, gases hazardous to health may be formed.
<b>Special protective equipment and precautions for firefighters</b>	Firefighters must use standard protective equipment including flame retardant coat, helmet with face shield, gloves, rubber boots, and in enclosed spaces, SCBA.
<b>Fire-fighting equipment/instructions</b>	Cool containers exposed to heat with water spray and remove container, if no risk is involved.
<b>General fire hazards</b>	No unusual fire or explosion hazards noted.

#### 6. Accidental release measures

<b>Personal precautions, protective equipment and emergency procedures</b>	Keep unnecessary personnel away. Keep people away from and upwind of spill/leak. Keep out of low areas. Wear appropriate protective equipment and clothing during clean-up. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Ensure adequate ventilation. Local authorities should be advised if significant spillages cannot be contained. For personal protection, see section 8 of the SDS.
--	---

**Methods and materials for containment and cleaning up**

The product is immiscible with water and will spread on the water surface.

Large Spills: Stop the flow of material, if this is without risk. Dike the spilled material, where this is possible. Cover with plastic sheet to prevent spreading. Absorb in vermiculite, dry sand or earth and place into containers. Following product recovery, flush area with water.

Small Spills: Sweep up or vacuum up spillage and collect in suitable container for disposal. Clean surface thoroughly to remove residual contamination.

Never return spills to original containers for re-use. For waste disposal, see section 13 of the SDS. Prevent entry into waterways, sewer, basements or confined areas.

**Environmental precautions**

Avoid discharge into drains, water courses or onto the ground. Use appropriate containment to avoid environmental contamination. Inform appropriate managerial or supervisory personnel of all environmental releases.

---

**7. Handling and storage**

**Precautions for safe handling**

Do not get in eyes, on skin, or on clothing. Avoid prolonged exposure. When using, do not eat, drink or smoke. Use only in well-ventilated areas. Wear appropriate personal protective equipment. Wash hands after handling and before eating. Wash contaminated clothing before reuse. Observe good industrial hygiene practices. Use appropriate container to avoid environmental contamination. For product usage instructions, please see the product label.

**Conditions for safe storage, including any incompatibilities**

Keep away from heat and sources of ignition. Store in a cool, dry place out of direct sunlight. Keep container tightly closed. Store in a well-ventilated place. Store away from incompatible materials (see Section 10 of the SDS).

---

**8. Exposure controls/personal protection**

**Occupational exposure limits**

**US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)**

Components	Type	Value	Form
White mineral oil (CAS 8042-47-5)	PEL	5 mg/m3	Mist.

**US. ACGIH Threshold Limit Values**

Components	Type	Value	Form
White mineral oil (CAS 8042-47-5)	TWA	5 mg/m3	Inhalable fraction.

**US. NIOSH: Pocket Guide to Chemical Hazards**

Components	Type	Value	Form
White mineral oil (CAS 8042-47-5)	STEL	10 mg/m3	Mist.
	TWA	5 mg/m3	Mist.

**Biological limit values**

No biological exposure limits noted for the ingredient(s).

**Appropriate engineering controls**

Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level. Provide eyewash station.

**Individual protection measures, such as personal protective equipment**

**Eye/face protection** Wear safety glasses with side shields (or goggles).

**Skin protection**

**Hand protection** Wear protective gloves such as: Latex.

**Other** Wear appropriate chemical resistant clothing. Use of an impervious apron is recommended.

**Respiratory protection** If engineering controls are not feasible or if exposure exceeds the applicable exposure limits, use a NIOSH-approved cartridge respirator with an organic vapor cartridge. Use a self-contained breathing apparatus in confined spaces and for emergencies. Air monitoring is needed to determine actual employee exposure levels.

**Thermal hazards** Wear appropriate thermal protective clothing, when necessary.

**General hygiene considerations**

Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants. Contaminated work clothing should not be allowed out of the workplace.

---

## 9. Physical and chemical properties

### Appearance

Physical state	Solid.
Form	Grease.
Color	Tan.
Odor	Mild. Petroleum.
Odor threshold	Not available.
pH	Not available.
Melting point/freezing point	Not available.
Initial boiling point and boiling range	450 °F (232.2 °C) estimated
Flash point	> 356 °F (> 180 °C) Cleveland Open Cup
Evaporation rate	Very slow.
Flammability (solid, gas)	Not available.
Upper/lower flammability or explosive limits	
Flammability limit - lower (%)	Not available.
Flammability limit - upper (%)	Not available.
Vapor pressure	1.2 hPa estimated
Vapor density	> 0.5 (air = 1)
Relative density	0.96
Solubility (water)	Insoluble.
Partition coefficient (n-octanol/water)	Not available.
Auto-ignition temperature	500 °F (260 °C) estimated
Decomposition temperature	Not available.
Viscosity (kinematic)	0.9 - 1.5 cm <sup>2</sup> /s (104 °F (40 °C))
Percent volatile	Not available.

---

## 10. Stability and reactivity

Reactivity	The product is stable and non-reactive under normal conditions of use, storage and transport.
Chemical stability	Material is stable under normal conditions.
Possibility of hazardous reactions	No dangerous reaction known under conditions of normal use.
Conditions to avoid	Contact with incompatible materials.
Incompatible materials	Strong oxidizing agents.
Hazardous decomposition products	Carbon oxides. Sulfur oxides. Metal oxides.

---

## 11. Toxicological information

### Information on likely routes of exposure

Ingestion	Expected to be a low ingestion hazard.
Inhalation	Prolonged or excessive inhalation may cause respiratory tract irritation. Prolonged inhalation may be harmful.
Skin contact	May cause an allergic skin reaction.
Eye contact	Causes serious eye irritation.
Symptoms related to the physical, chemical and toxicological characteristics	Rash. Severe eye irritation. Symptoms may include stinging, tearing, redness, swelling, and blurred vision. Skin irritation. May cause an allergic skin reaction. Dermatitis.

### Information on toxicological effects

Acute toxicity	May cause an allergic skin reaction.
----------------	--------------------------------------

Product	Species	Test Results
Extreme Duty Food Grade Grease		
<b>Subchronic</b>		
<i>Oral</i>		
LD50	Rat	7960 g/kg, 14 days estimated

\* Estimates for product may be based on additional component data not shown.

<b>Skin corrosion/irritation</b>	Prolonged skin contact may cause temporary irritation.
<b>Serious eye damage/eye irritation</b>	Causes serious eye irritation.
<b>Respiratory sensitization</b>	Not available.
<b>Skin sensitization</b>	May cause an allergic skin reaction.
<b>Germ cell mutagenicity</b>	No data available to indicate product or any components present at greater than 0.1% are mutagenic or genotoxic.
<b>Carcinogenicity</b>	This product is not considered to be a carcinogen by IARC, ACGIH, NTP, or OSHA.
<b>IARC Monographs. Overall Evaluation of Carcinogenicity</b>	
White mineral oil (CAS 8042-47-5)	3 Not classifiable as to carcinogenicity to humans.
<b>Reproductive toxicity</b>	This product is not expected to cause reproductive or developmental effects.
<b>Specific target organ toxicity - single exposure</b>	Not classified.
<b>Specific target organ toxicity - repeated exposure</b>	Not classified.
<b>Aspiration hazard</b>	Not likely, due to the form of the product.
<b>Chronic effects</b>	Prolonged inhalation may be harmful.

## 12. Ecological information

<b>Ecotoxicity</b>	The product is not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.
<b>Persistence and degradability</b>	Not readily biodegradable.
<b>Bioaccumulative potential</b>	No data available.
<b>Mobility in soil</b>	No data available.
<b>Other adverse effects</b>	No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.

## 13. Disposal considerations

<b>Disposal of waste from residues / unused products</b>	This product is not a RCRA hazardous waste (See 40 CFR Part 261.20 – 261.33). Empty containers may be recycled. Collect and reclaim or dispose in sealed containers at licensed waste disposal site. Dispose in accordance with all applicable regulations.
<b>Hazardous waste code</b>	Not regulated.
<b>Contaminated packaging</b>	Empty containers should be taken to an approved waste handling site for recycling or disposal. Since emptied containers may retain product residue, follow label warnings even after container is emptied.

## 14. Transport information

<b>DOT</b>	Not regulated as dangerous goods.
<b>IATA</b>	Not regulated as dangerous goods.
<b>IMDG</b>	Not regulated as dangerous goods.

## 15. Regulatory information

<b>US federal regulations</b>	This product is a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200. All components are on the U.S. EPA TSCA Inventory List.
-------------------------------	---

**TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)**

Not regulated.

**SARA 304 Emergency release notification**

Not regulated.

**US. OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)**

Not listed.

**US EPCRA (SARA Title III) Section 313 - Toxic Chemical: Listed substance**

Not listed.

**CERCLA Hazardous Substance List (40 CFR 302.4)**

Calcium dodecylbenzenesulphonate (CAS 26264-06-2)

**CERCLA Hazardous Substances: Reportable quantity**

Calcium dodecylbenzenesulphonate (CAS 26264-06-2) 1000 LBS

Spills or releases resulting in the loss of any ingredient at or above its RQ require immediate notification to the National Response Center (800-424-8802) and to your Local Emergency Planning Committee.

**Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List**

Not regulated.

**Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)**

Not regulated.

**Safe Drinking Water Act (SDWA)** Not regulated.

**Food and Drug Administration (FDA)** Not regulated.

**Superfund Amendments and Reauthorization Act of 1986 (SARA)**

**Section 311/312** Immediate Hazard - Yes

**Hazard categories** Delayed Hazard - No  
Fire Hazard - No  
Pressure Hazard - No  
Reactivity Hazard - No

**SARA 302 Extremely hazardous substance** No

**US state regulations**

**US. California Controlled Substances. CA Department of Justice (California Health and Safety Code Section 11100)**

Not listed.

**US. New Jersey Worker and Community Right-to-Know Act**

Calcium dodecylbenzenesulphonate (CAS 26264-06-2)

Diboron calcium tetraoxide (CAS 13701-64-9)

**US. Massachusetts RTK - Substance List**

Calcium dodecylbenzenesulphonate (CAS 26264-06-2)

White mineral oil (CAS 8042-47-5)

**US. Pennsylvania Worker and Community Right-to-Know Law**

Calcium dodecylbenzenesulphonate (CAS 26264-06-2)

White mineral oil (CAS 8042-47-5)

**US. Rhode Island RTK**

Calcium dodecylbenzenesulphonate (CAS 26264-06-2)

**US. California Proposition 65**

California Safe Drinking Water and Toxic Enforcement Act of 1986 (Proposition 65): This material is not known to contain any chemicals currently listed as carcinogens or reproductive toxins.

**Volatile organic compounds (VOC) regulations**

**EPA**

**VOC content (40 CFR 51.100(s))** 0 %

**Consumer products (40 CFR 59, Subpt. C)** Not regulated

**State**

**Consumer products** Not regulated

**VOC content (CA)** 0 %

**VOC content (OTC)** 0 %

## International Inventories

Country(s) or region	Inventory name	On inventory (yes/no)*
Australia	Australian Inventory of Chemical Substances (AICS)	No
Canada	Domestic Substances List (DSL)	No
Canada	Non-Domestic Substances List (NDSL)	Yes
China	Inventory of Existing Chemical Substances in China (IECSC)	Yes
Europe	European Inventory of Existing Commercial Chemical Substances (EINECS)	No
Europe	European List of Notified Chemical Substances (ELINCS)	No
Japan	Inventory of Existing and New Chemical Substances (ENCS)	No
Korea	Existing Chemicals List (ECL)	No
New Zealand	New Zealand Inventory	No
Philippines	Philippine Inventory of Chemicals and Chemical Substances (PICCS)	No
United States & Puerto Rico	Toxic Substances Control Act (TSCA) Inventory	Yes

\*A "Yes" indicates that all components of this product comply with the inventory requirements administered by the governing country(s)

A "No" indicates that one or more components of the product are not listed or exempt from listing on the inventory administered by the governing country(s).

---

## 16. Other information, including date of preparation or last revision

Issue date	12-16-2014
Prepared by	Allison Cho
Version #	01
Further information	Not available.
HMIS® ratings	Health: 1 Flammability: 1 Physical hazard: 0 Personal protection: B
NFPA ratings	Health: 1 Flammability: 1 Instability: 0

### NFPA ratings



### Disclaimer

CRC cannot anticipate all conditions under which this information and its product, or the products of other manufacturers in combination with its product, may be used. It is the user's responsibility to ensure safe conditions for handling, storage and disposal of the product, and to assume liability for loss, injury, damage or expense due to improper use. The information contained in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. This information is accurate to the best of CRC Industries' knowledge or obtained from sources believed by CRC to be accurate. Before using any product, read all warnings and directions on the label. For further clarification of any information contained on this (M)SDS consult your supervisor, a health & safety professional, or CRC Industries.