iCAST Series

HAVE A SMART BLAST!

THE ONLY INTELLIGENT MARKETING & ADVERTISING MATERIAL PLATFORM HAND DRYER WITH WIFI. GSM & LAN TECHNOLOGY IN THE INDUSTRY

FEATURES


- Vandal proof-not scratchable with any sharp object
- Fastest drying time on the market
- Automatic infrared actuated sensor, for power conservation and maximum hygiene
- Exclusive: Adjustable output airflow temperature
- Robust, vandal proof, tamper-proof design and construction for greater product durability and longevity
- lifetime warranty the best one in the industry
- High velocity (100 CFM) airflow for ultra high speed hand drying: 8 sec.
- 5.5 inches touch screen, full WiFi, GSM, Ethernet, Bluetooth connectivity for data upload & remote dryer maintenance
- Unique interactive communication between the machine and the end user, full WiFi monitoring worldwide
- Radio FM/AM worldwide (option)
- · Smallest footprint on the market
- Universal voltage: automatic voltage switching for ease of installation
- Designed for easy installation
- Contributes to LEED and BOMA building certifications
- Vandal proof ABS plexiglass screen protector
- Tamperproof screws
- Fire Alarm and Active Shooter Alarm (optional)













APPLICATIONS

- All public and commercial bathrooms and clean up areas. Factories, restaurants, pools, gyms, hospitals and schools
- All facilities with a need for advertising
- · Marketing and advertising companies for better reach of target audiences
- Great platform to reach employees and staff internally
- Made for high traffic public areas



DIMENSIONS

















Voltage Universal 115-230*VAC (*50/60Hz)

Wattage 1450 W at 5.2A (230VAC)

Motor Vacuum Motor, 36,000 RPM (outside the enclosure) 5/8HP 20,000 RPM (installed in the enclosure)

Colour White, Black and Stainless Steel

Finish Chrome, scratch-resistant porcelain,

brushed stainless steel.

Heating Element 725w resistance coil. **Construction Material** Reinforced Steel

Controls & Wiring Automatic resetting thermostat with cutout when airflow is restricted. Infrared sensor cutout two seconds after hand removal, and 85 seconds after initiating drying.

Installation Removable predrilled baseplate for easy mounting.

Warranty LIFETIME

CSA certified for use in Canada and the U.S. CE approved for use where applicable.

Patent Pending

ORDERING GUIDE

Model No.	Color	Watts cold air hot air	Volts Hz	Air Velocity LFM	Air Volume CFM	Noise dB	Dimensions (W x H x D) (mm/in.)	Weight (kg/lbs.)
c-400000000	White	725-1450	115-230,50-60	19,000	100	78	235 x 280 x 170 (9.25 x 11.02 x 6.69)	5/11
C-40000002	Black	725-1450	115-230, 50-60	19,000	100	78	235 x 280 x 170 (9.25 x 11.02 x 6.69)	5/11
C-400220000	Brushed stainless steel	725-1450	115-230, 50-60	19,000	100	78	235 x 280 x 170 (9.25 x 11.02 x 6.69)	5/11
C-400230000	Chrome	725-1450	115-230, 50-60	19,000	100	78	235 x 280 x 170 (9.25 x 11.02 x 6.69)	5/11



















