

















MISTRAL 201 BL D2 is a lightweight vacuum designed for performance and movement speed. It's ideal for small-medium dust with potentially combustible properties, and it has a large filter surface to reduce clogging.



Features

- Compact, portable and constructed with powder coated steel
- ✓ Spark-free brushless motor (up to 10,000 hour life expectancy)
- ✓ Bonding and grounding
- ✓ Removable stainless steel collection tank
- ✓ DUSTOP reverse pulse cleaning system
- √ Large filter surface
- ✓ Performance indicator light
- ✓ NRTL certified for Class II, Division 2 hazardous locations

Filtration

Primary Filter	Cartridge
Surface Area	32 ft ² (3 m ²)
Media Class (IEC 60335-2-69)	Antistatic Polyester - Class M
Cleaning System	DUSTOP

Optionals

- Safe dust bag system
- Certified HEPA Class H14 (99.995% @ 0.18 μm)
- Partial or Full Stainless Steel Frame
- More Power Sources Available By Request
- Other Certifications Available By Request

MISTRAL 201 BL D2

Voltage	V - Hz	115 - 60 1~
Power	HP (kW)	1.5 (1.1)
Max Water Lift	inH2O (mmH2O)	90.6 (2300)
Max Max Airflow	CFM (m³/h)	121.8 (207)
Electrical Protection	IP Class	Explosion Proof
Capacity	gal (L)	5 (20)
Dimensions	in (WxLxH)	19 x 23 x 43
Weight	lbs (kg)	77 (35)
Noise Level (EN ISO 3744)	dB(A)	78
Suction Inlet	in (mm)	2 (50)