

MISTRAL 202 DS is a lightweight vacuum designed for performance and movement speed. It's ideal for small-medium dust, and it comes with a long list of customization features.

Features

- ✓ Compact, portable and constructed with powder coated steel
- ✓ 2 powerful bypass motors with independent cooling
- ✓ Cord wrap
- ✓ Removable collection tank
- ✓ DUSTOP reverse pulse cleaning system
- ✓ Safe for high-heat applications (up to 450° F)
- ✓ Large filter surface
- ✓ Performance indicator light

Filtration

Primary Filter	Cartridge
Surface Area	32 ft ² (3 m ²)
Media Class (IEC 60335-2-69)	PTFE Coated Polyester - Class M
Cleaning System	DUSTOP
Air Load - ft/min (m/h)	6.6 (120)

NRTL certified versions available for Div. 1 or Div. 2



Optionals

- Certified HEPA Class H14 (99.995% @ 0.18 µm)
- Antistatic Filter (Class M)
- NOMEX Heat Resistant Filter
- Earth Grounding
- LONGOPAC Safe Bagging System
- Partial or Full Stainless Steel Frame
- Remote Control
- Disposable Bags
- NRTL Certified Version (Class II, Div. 2)
- NRTL Certified Version (Classes I & II, Div. 1)
- More Power Sources Available By Request

MISTRAL 202 DS

Voltage	V - Hz	115 - 60 1~
Power	HP (kW)	1.5 (1.1)
Max Water Lift	inH2O (mmH2O)	90.1 (2289)
Max Airflow	CFM (m ³ /h)	211.9 (360)
Capacity	gal (L)	5 (20)
Dimensions	in (WxLxH)	23 x 19 x 43
Weight	lbs (kg)	77 (35)
Noise Level (EN ISO 3744)	dB(A)	76
Suction Inlet	in (mm)	2 (50)