

I-sani



FEATURES

- Vandal proof-not scratchable with any sharp object
- Fastest drying time on the market
- Automatic infrared actuated sensor, for power conservation and maximum hygiene
- **Exclusive: Adjustable output airflow temperature**
- Robust, vandal proof, tamper-proof design and construction for greater product durability and longevity
- lifetime warranty - the best one in the industry
- High velocity (100 CFM) airflow for ultra high speed hand drying: 8 sec.
- 10.1 inches touch screen, full WiFi, GSM, Ethernet, Bluetooth connectivity for data upload & remote dryer maintenance
- Unique interactive communication between the machine and the end user, full WiFi monitoring worldwide
- Radio FM/AM worldwide (option)
- **500 ml Sanitizer Dispenser**
- Universal voltage: automatic voltage switching for ease of installation
- Designed for easy installation
- Contributes to LEED and BOMA building certifications
- Vandal proof ABS plexiglass screen protector
- Tamperproof screws
- Fire Alarm and Active Shooter Alarm (optional)
- **HEPA Cartridge with Foam Prefilter**

SPECIFICATIONS

Voltage Universal 115-230*VAC (*50/60Hz)

Wattage 1000W at 4.3A (230VAC)

Motor Vacuum Motor, 36,000 RPM (outside the enclosure)
5/8HP 20,000 RPM (installed in the enclosure)

Colour White, Black and Stainless Steel

Finish Chrome, scratch-resistant porcelain, brushed stainless steel.

Heating Element 400w resistance coil.

Construction Material Reinforced Steel


Noise 75dB

APPLICATIONS

- All public and commercial bathrooms and clean up areas. Factories, restaurants, pools, gyms, hospitals and schools
- All facilities with a need for advertising
- Marketing and advertising companies for better reach of target audiences
- Great platform to reach employees and staff internally
- Made for high traffic public areas

DIMENSIONS

BACK VIEW



SIDE VIEW

