

MISTRAL 202 D1 is a single-phase vacuum designed for performance and flexibility. Having been NRTL tested and certified for Classes I & II, it's the perfect solution for enclosed areas where dust is constantly present in the air.

Features

- ✓ Compact, portable and constructed with conductive powder coated steel
- ✓ Spark-free brushless motor (up to 10,000 hour life expectancy)
- ✓ Bonding and grounding
- ✓ Removable stainless steel collection tank and filter chamber
- ✓ Performance indicator light
- ✓ DUSTOP reverse pulse cleaning system
- ✓ Large filter surface
- ✓ Certified HEPA Class H14 (99.995% @ 0.18 µm) as standard
- ✓ **NRTL certified for Classes I and II, Division 1 hazardous locations**

Filtration

Primary Filter	Cartridge
Surface Area	32 ft ² (3 m ²)
Media Class (IEC 60335-2-69)	Antistatic Polyester - Class M
Cleaning System	DUSTOP
HEPA Filter (Included)	Certified H14 Class (99.995% @ 0.18 µm)

NRTL CERTIFIED FOR CLASSES I&II, DIVISION 1

Groups D, E, F, G



Optionals

- Partial or Full Stainless Steel Frame
- More Power Sources Available By Request
- Other Certifications Available By Request

MISTRAL 202 D1

Voltage	V - Hz	115 - 60 1~
Power	HP (kW)	0.9 (0.7)
Max Water Lift	inH2O (mmH2O)	67.7 (1720)
Max Max Airflow	CFM (m ³ /h)	138.3 (235)
Electrical Protection	IP Class	Explosion Proof
Capacity	gal (L)	5 (20)
Dimensions	in (WxLxH)	19 x 23 x 43
Weight	lbs (kg)	88 (40)
Noise Level (EN ISO 3744)	dB(A)	80
Suction Inlet	in (mm)	2 (50)