

ZEFIRO EV AP 560 PN is a compact dust collector for large volumes of dry powder. It has an automatic cleaning system with 4 rotating filter cartridges to maximize performance and reduce downtime.

Features

- ✓ Compact and constructed with powder coated steel
- ✓ Electric fan for high airflow
- ✓ Ideal for 24/7 production cycles
- ✓ Large filter surface
- ✓ Bonding and grounding
- ✓ Accessory basket
- ✓ Removable stainless steel collection tank
- ✓ Nylon air exhaust diffuser
- ✓ Pneumatic reverse pulse cleaning system
- ✓ Optional arm for localized suction

Filtration

Primary Filter	4 Cartridges
Surface Area	114 ft ² (10.6 m ²)
Media Class (IEC 60335-2-69)	Antistatic Polyester - Class M
Cleaning System	Automatic Pneumatic



Optionals

- Extraction Arm
- Double Extraction Arm
- Manual Cleaning System
- Partial or Full Stainless Steel Frame
- More Power Sources Available By Request
- NFPA 652 compliant and ATEX certified for Zone 22

EV AP 560 PN (3 HP)

EV AP 560 PN (5 HP)

Voltage	V - Hz	230/460 - 60 3~	230/460 - 60 3~
Power	HP (kW)	3.5 (2.6)	6.4 (4.8)
Continuous Water Lift	inH ₂ O (mmH ₂ O)	15.7 (400) / 15.7 (400)	15.7 (400) / 15.7 (400)
Max Airflow	CFM (m ³ /h)	1059.4 (1800)	1059.4 (1800)
Electrical Protection	IP Class	55	55
Capacity	gal (L)	26 (100)	26 (100)
Dimensions	in (WxLxH)	31 x 33 x 98	31 x 33 x 98
Weight	lbs (kg)	276 (125)	309 (14)
Noise Level	dB(A)	72	74
Suction Inlet	in (mm)	8 (200)	6 (150)