

Bench Grinders – IGB-8 / IGB-10



- ◆ 8" Industrial bench grinder
- ◆ 3600 rpms
- ◆ LED light included
- ◆ Enclosed pre-lubricated ball bearings
- ◆ Rubber mounts
- ◆ One-piece quick adjusting spark guards
- ◆ Adjustable tool rests
- ◆ 1-1/4" dresser included
- ◆ CSA listed
- ◆ 115V

| SPECIFICATIONS – IGB-8 | |
|---------------------------------|------------------|
| Wheel Size | 8" x 1" x 5/8" |
| Wheel Type | Aluminum Oxide |
| Wheel Grits | 36 & 60 |
| Shaft Diameter | 5/8" |
| Motor HP | 1" |
| Motor Speed | 3,600 rpm |
| Power Requirements | 115V |
| Decibels | 75dB @ 3' |
| Foot Print | 9-1/2" x 8-1/16" |
| Distance between Mounting Holes | 8-1/2" |
| Shipping Dimensions | 23" x 14" x 14" |
| Shipping Weight | 75 lbs. |

Specifications subject to change without notice.



- ◆ 10" Industrial bench grinder
- ◆ 1800 rpms
- ◆ LED light included
- ◆ Enclosed pre-lubricated ball bearings
- ◆ Rubber mounts
- ◆ One-piece quick adjusting spark guards
- ◆ Adjustable tool rests
- ◆ Dia. 1-1/4" dresser included
- ◆ CSA listed
- ◆ 115V

| SPECIFICATIONS – IGB-10 | |
|---------------------------------|---------------------|
| Wheel Size | 10" x 1" x 1" |
| Wheel Type | Aluminum Oxide |
| Wheel Grits | 36 & 60 |
| Shaft Diameter | 1" |
| Motor HP | 1-1/2" |
| Motor Speed | 1,800 rpm |
| Power Requirements | 115V |
| Decibels | 75dB @ 3' |
| Foot Print | 10" x 9-5/8" |
| Distance between Mounting Holes | 8-3/4" |
| Shipping Dimensions | 34" x 13" x 15-1/2" |
| Shipping Weight | 125 lbs. |

Specifications subject to change without notice.