



















DG KW6 D2 is a series of NRTL tested and certified vacuums for the continuous collection of medium dust. They are recognized as Delfin's most versatile three-phase systems in the explosion-proof line.



Features

- ✓ Compact, portable and constructed with powder coated steel
- Side channel blower (continuous use / no maintenance up to 30,000 hours)
- Bonding and grounding
- Stainless steel removable tank
- Tangential inlet with cyclone filter protector
- Large filter surface
- Integrated cleaning system
- Pressure relief valve
- NRTL certified for Class II, Division 2 hazardous locations

Filtration

Primary Filter	Star
Surface Area	32 ft ² (3 m ²)
Media Class (IEC 60335-2-69)	Antistatic Polyester - Class M
Cleaning System	Manual

Optionals

- Certified HEPA Class H14 (99.995% @ 0.18 μm)
- Partial or Full Stainless Steel Frame
- More Power Sources Available By Request
- Other Certifications Available By Request

DG KW6 D2

Voltage	V - Hz	460 - 60 /3~
Power	HP (kW)	8.4 (6.3)
Continuous Water Lift	inH2O (mmH2O)	78.3 (1988)
Max Max Airflow	CFM (m³/h)	353.1 (600)
Electrical Protection	IP Class	55
Capacity	gal (L)	26 (100)
Dimensions	in (WxLxH)	26 x 47 x 57
Weight	lbs (kg)	320 (145)
Noise Level (EN ISO 3744)	dB(A)	74
Suction Inlet	in (mm)	3 (80)