

English Wheels – EW-30

SPECIFICATIONS – EW-30

Capacity		
Mild Steel	10 ga.	
Aluminum	0.125 (Soft)	3.175 mm
Throat Depth	30"	940 mm
Lower Die Radii (inch)	Flat, 36, 24, 12, 8, 6, 4, 2	
Lower Wheel Dimensions	3"	76.2 mm
Top Wheel Dimensions	10" Dia. x 3.0	254 x 76.2 mm
Shipping Dimensions (L x W x H)	48" x 48" x 84"	1220 x 1220 x 2134 mm
Shipping Weight	1,000 lbs.	454 kgs.

Specifications subject to change without notice.

- ◆ 30" throat depth
- ◆ Ridged twin plate design
- ◆ Integrated roll holder
- ◆ 10" x 3" upper wheel
- ◆ Locking cam quick release
- ◆ Includes 7 lower anvils

