

# 3-in-1 Shear / Brake / Roll – SBR-3020 / SBR-4020

| SPECIFICATIONS – SBR-3020       |                 |                    |
|---------------------------------|-----------------|--------------------|
| Bed Width                       | 30"             | 762 mm             |
| Shear Capacity                  | 20 ga. (.036")  | 1 mm               |
| Bending Capacity                | 20 ga. (.036")  | 1 mm               |
| Rolling Capacity                | 20 ga. (.036")  | 1 mm               |
| Maximum Bend Angle              | 90°             |                    |
| Minimum Rolling Dia.            | 1.54"           | 39 mm              |
| Power Requirement               | Manual          |                    |
| Shipping Dimensions (L x W x H) | 38" x 18" x 27" | 965 x 457 x 686 mm |
| Shipping Weight                 | 363 lbs.        | 165 kgs.           |

Specifications subject to change without notice.

- ◆ Combination shear, sheet metal brake, and slip roll
- ◆ 30" forming width
- ◆ 20-gauge mild steel capacity
- ◆ Manually operated
- ◆ Segmented fingers on brake
- ◆ 3-wire grooves
- ◆ 4 sided blades
- ◆ Bench mounted

- ◆ Combination shear, sheet metal brake, and slip roll
- ◆ 40" forming width
- ◆ 20-gauge mild steel capacity
- ◆ Manually operated
- ◆ Segmented fingers on brake
- ◆ 3-wire grooves
- ◆ Bench mounted
- ◆ 4 sided blades

| SPECIFICATIONS – SBR-4020       |                 |                      |
|---------------------------------|-----------------|----------------------|
| Bed Width                       | 40"             | 1,016 mm             |
| Shear Capacity                  | 20 ga. (.036")  | 1 mm                 |
| Bending Capacity                | 20 ga. (.036")  | 1 mm                 |
| Rolling Capacity                | 20 ga. (.036")  | 1 mm                 |
| Maximum Bend Angle              | 90°             |                      |
| Minimum Rolling Dia.            | 1.70"           | 43 mm                |
| Power Requirement               | Manual          |                      |
| Shipping Dimensions (L x W x H) | 53" x 18" x 27" | 1,346 x 457 x 686 mm |
| Shipping Weight                 | 467 lbs.        | 212 kgs.             |

Specifications subject to change without notice.



SBR-3020



SBR-4020