

3-in-1 Shear / Brake / Roll – SBR-5216

- ◆ Combination shear, sheet metal brake, and slip roll
- ◆ 52" forming width
- ◆ 16-gauge mild steel capacity
- ◆ Manually operated
- ◆ Segmented fingers on brake
- ◆ 3-wire grooves
- ◆ Bench mounted
- ◆ 4 sided blades

SPECIFICATIONS – SBR-5216		
Bed Width	52"	1,321 mm
Shear Capacity	16 ga. (.060")	1.5 mm
Bending Capacity	16 ga. (.060")	1.5 mm
Rolling Capacity	16 ga. (.060")	1.5 mm
Diameter of Rolls	2.38"	60.5 mm
Maximum Bend Angle	90°	
Minimum Rolling Dia.	3.57"	91 mm
Power Requirement	Manual	
Shipping Dimensions (LxWxH)	67" x 30" x 46"	1,702 x 762 x 1,168 mm
Shipping Weight	1,200 lbs.	544 kgs.

Specifications subject to change without notice.

