

Manual Band Saws – BS-916M / BS-300M

SPECIFICATIONS – BS-916M

Capacity		
Round (90°/45°)	8.85" / 6.5"	225 mm / 165 mm
Square (90°/45°)	8.85" / 6.5"	225 mm / 165 mm
Rectangular (90°/45°)	8.85" x 13.5" / 8.85" x 6.5"	225 x 343 / 225 x 165 mm
Blade Size (H x W x L)	1" / .035" / 119.48"	25 mm / .889 mm / 3035 mm
Blade Speed (fpm)	82 / 132 / 170 / 235	
Blade Guide	Roller	
Miter Angle	0 – 45°	
Miter Adjustment	Vise	
Table Height	24"	610 mm
Descent Control	Hydraulic	
Return	Manual	
Drive	Belt / Pulley	
Motor	1.5 hp	
Power	220V / 1-Phase	
Shipping Dimensions (L x W x H)		
	68" x 30" x 43"	1727 x 762 x 1092 mm
Shipping Weight	700 lbs.	319 kgs.

Specifications subject to change without notice.

- ◆ Cuts metal and more
- ◆ 1" blade standard
- ◆ Hydraulic descent
- ◆ Automatic shut-off
- ◆ 4 blade speeds
- ◆ 220V 1-phase



BS-300M

- ◆ Cuts metal and more
- ◆ 1" blade standard
- ◆ Hydraulic descent
- ◆ Automatic shut-off
- ◆ 4 blade speeds
- ◆ 220V 1-phase



BS-916M

SPECIFICATIONS – BS-300M

Capacity		
Round (90°/45°)	9.84" / 7.5"	250 mm / 190 mm
Square (90°/45°)	9.84" / 7.5"	250 mm / 190 mm
Rectangular (90°/45°)	9.84" x 16.33" / 9.84" x 7.50"	250 x 414 / 250 x 190 mm
Blade Size (H x W x L)	1" / .035" / 129.92"	25 mm / .889 mm / 3300 mm
Blade Speed (fpm)	66 / 131 / 167 / 233	
Blade Guide	Roller	
Miter Angle	0 – 45°	
Miter Adjustment	Vise	
Table Height	30.7"	780 mm
Descent Control	Hydraulic	
Return	Manual	
Drive	Belt / Pulley	
Motor	2 hp	
Power	220V / 1-Phase	
Shipping Dimensions (L x W x H)		
	70" x 23" x 49"	1778 x 584 x 1245 mm
Shipping Weight	800 lbs.	364 kgs.

Specifications subject to change without notice.