

# Rotary Draw Benders – RDB-050



Specifications – RDB-050		
Mild Steel Pipe (Schedule 40)	Call for Details	Call for Details
Aluminum Pipe (Schedule 40)	Call for Details	Call for Details
Stainless Steel Pipe (Schedule 40)	Call for Details	Call for Details
Mild Steel Round Tube (Wall)	2.50" (.120)	64 mm x 3 mm
Aluminum Round Tube (Wall)	2.50" (.120)	64 mm x 3 mm
Stainless Steel Round Tube (Wall)	2.00" (.120)	50 mm x 3 mm
Chromolly Round Tube (Wall)	2.00" (.120)	50 mm x 3 mm
Mild Steel Solid Rod	1.0"	25 mm
Mild Steel Square Tube (Wall)	N/A	N/A
Minimum OD	.75"	19 mm
Maximum Speed to 180 Degrees	N/A	N/A
Maximum Center Line Radius (CLR)	7.00"	176 mm
Minimum CLR	3.00"	76 mm
Power Requirements	N/A	N/A
Weight (Lbs.)	290	132 kg.
Length	44.00"	1118 mm
Width	27.00"	686 mm
Height	42.00"	1067 mm

Specifications subject to change without notice.

The RDB-050 is a manually operated Tube Bender with huge capacity at an economical price.

- ◆ Dies available for 90 or 180 degrees
- ◆ Replaceable bronze bushings at all pivot points
- ◆ Three bending speeds
- ◆ 180 degree bends, without repining the die
- ◆ Anti-spring back mechanism included
- ◆ Integrated degree dial included
- ◆ Quick change hook sleeve inserts, no u-straps
- ◆ US patent no. 8,171,705