

# Metal Dust Collectors – MDC-1200-HD



Cartridge filter



Filter removal



Hepa filter



SPECIFICATIONS – MDC-1200-HD		
Air Capacity	1100 CFM	
Noise	75 dB	
Filter	HEPA Cartridge	
Filter Size	Ø15" x 26"L	Ø380 mm x 660 mm
Inlet Size	6"	152.4 mm
Motor	1.5 hp	
Power Requirements	110V	
Shipping Dimensions (L x W x H)	34.7" x 25.8" x 68.2"	879.8 x 656 x 1731 mm
Shipping Weight	550 lbs.	250 kgs.

*Specifications subject to change without notice.*

- ◆ Heavy duty metalworking dust collector
- ◆ 1.5 hp
- ◆ 1100 CFM
- ◆ Pulse clean filter cartridge system (air supply required)
- ◆ Fire resistant teflon coated filter
- ◆ Magnehelic pressure gauge
- ◆ Full steel construction
- ◆ HEPA filter standard
- ◆ Tool-less filter maintenance
- ◆ CSA – U.S. certified
- ◆ 110V