

Tube & Pipe Notchers – TN-210H / TN-250

SPECIFICATIONS – TN-210H

Notching Capacity (OD)	2"	50.8 mm
Spindle Size	1"	25 mm
Spindle Adapter	1/2" and 5/8"	
Angle Adjustment	0–50°	
Power Requirements	Drill Press or Hand Drill	
Shipping Dimensions (L x W x H)	12" x 7" x 5"	305 mm x 178 mm x 128 mm
Shipping Weight	10 lbs.	5 kgs.

Specifications subject to change without notice.



TN-210H
Shown with
optional hole saw

**DON'T FORGET THE
HOLE SAWS!**

SPECIFICATIONS – TN-250

Notching Capacity (OD)	1/2" – 2-1/2"	12.7 mm – 63.5 mm
Angle Adjustment	Infinite	
Power Requirements	1/2" (12.7 mm) Hand Drill	
Shipping Dimensions (L x W x H)	24" x 12" x 12"	610 mm x 305 mm x 305 mm
Shipping Weight	50 lbs.	23 kgs.

Specifications subject to change without notice.



TN-250
Shown with
optional hole saw

- ◆ Unique 6 jaw radial vise
- ◆ Will notch over 75°
- ◆ 1-1/4" hardened Thomson shaft with replaceable tips
- ◆ Slotted carriage for offset notches (no shims)
- ◆ Patent #8,734.066