

# Slip Rolls – SR-5016M

- ◆ 50" forming width
- ◆ 16-gauge mild steel capacity
- ◆ Manually powered
- ◆ 3-wire grooves
- ◆ Optional floor stand
- ◆ 2" back roll adjustment
- ◆ Top roll swings out for material removal

SPECIFICATIONS – SR-5016M		
Forming Width	50"	1,270 mm
Capacity (Mild Steel)	16 ga. (.060")	1.5 mm
Upper Roll Dia.	3"	76.2 mm
Minimum Forming Dia.	4.5"	114 mm
Wire Grooves		
(1)	.335"	8.5 mm
(2)	.407"	10.3 mm
(3)	.513"	13 mm
Gear Ratio	3:1	
Stand	Optional	
Power Requirement	Manual	
Shipping Dimensions (L x W x H)	65" x 16" x 20"	1651 x 406 x 508 mm
Shipping Weight	528 lbs.	239 kgs.

*Specifications subject to change without notice.*



*Shown with optional floor stand – SKU 1007355*