

Corner Notchers – SN-F11-AN / SN-F09-MS

SPECIFICATIONS – SN-F11-AN		
Max. Capacity (SS)	11 ga. (15 ga.)	
Max. Notch Dimensions	5" x 5"	127 mm x 127 mm
Notch Angle	90° (Fixed)	
Strokes/Minute	50	
Blade Gap Adjustment	Manual	
Table Dimensions	18" x 23.5"	457 mm x 597 mm
Motor	N/A	
Working Pressure	115 psi	
Shipping Dimensions (L x W x H)	60" x 44" x 68"	1524 x 1118 x 1727 mm
Shipping Weight	500 lbs.	228 kgs.

Specifications subject to change without notice.

- ◆ Pneumatic operation
- ◆ 90° fixed angle
- ◆ Cuts up to 11-gauge (3 mm)
- ◆ 5" x 5" notch size
- ◆ Adjustable material stops
- ◆ Optional blades for stainless steel
- ◆ 4.4 gallons of air/notch



SN-F11-AN

- ◆ 90° fixed angle
- ◆ Cuts up to 9-gauge (4 mm)
- ◆ 7-3/4" x 7-3/4" notch size
- ◆ Manual blade gap adjustment
- ◆ Adjustable material stops
- ◆ Optional blades for stainless steel
- ◆ 220V 3-phase

SPECIFICATIONS – SN-F09-MS		
Max. Capacity (SS)	9 ga. (13 ga.)	
Max. Notch Dimensions	7-3/4" x 7-3/4"	197 mm x 197 mm
Notch Angle	90° (Fixed)	
Strokes/Minute	50	
Blade Gap Adjustment	Manual	
Table Dimensions	27" x 23.5"	685 mm x 597 mm
Motor	3 HP	
Power	220V / 3-phase	
Shipping Dimensions (L x W x H)	60" x 44" x 68"	1524 x 1118 x 1727 mm
Shipping Weight	1,100 lbs.	500 kgs.

Specifications subject to change without notice.

SN-F09-MS

