

# Metal Down Draft Tables – DDTM-4840-HD

## SPECIFICATIONS – DDTM-4840-HD

Table Size	48" x 40"	1240 mm x 1030 mm
Table Surface	Open Grate System	
CFM	1350 at Base	
Face Velocity	244 FPM	
Filter System	3 Stage	
Stage 1 Filter	Aluminum Mesh	
Stage 1 Filter Size	11.3" x 23.8" x 0.86"	285 x 630 x 22 mm
Stage 2 Filter	Polyester Teflon Coated Cartridge with Pulse Clean	
Stage 2 Filter Size	Ø11.25" x 13"L	Ø385 x 330 mm L
Stage 3 Filter	HEPA	
Stage 3 Filter Size	18" x 20" x 5.9"	457 x 508 x 150 mm
Required Air Supply	60–90 psi (For Pulse Clean Feature)	
Motor	1.5 hp	
Power Requirements	230V 3 Phase	
Shipping Dimensions (L x W x H)	58.8" x 39.3" x 73.6"	1493 x 998 x 1869 mm
Shipping Weight	1,019 lbs.	468 kgs.

Specifications subject to change without notice.

- ◆ 48" x 40" working area
- ◆ Heavy duty metalworking down draft table
- ◆ Perfect for grinding or sanding
- ◆ 2 hp
- ◆ 1350 CFM
- ◆ 3 stage filter
  1. Fire resistant aluminum
  2. Pulse clean filter system (air supply required)
  3. HEPA filter
- ◆ Easy clean out chip tray
- ◆ Full steel construction
- ◆ Includes side and back panels
- ◆ Integrated work light
- ◆ 110V aux. outlet
- ◆ Aux. air port
- ◆ CSA – U.S. certified
- ◆ 230V 3 phase



Cartridge filter



Chip tray



Hepa filter