



a nuvik⁺ brand

SAFETY DATA SHEET

SECTION 1 PRODUCT AND COMPANY INFORMATION

Product Name(s): Crocodile Cloth - AUTO
Product Code(s): 6930
Uses: Single use disposable wipes for personal/hand cleaning.
Company: Nuvik USA Inc.
Address: 950 Claycraft Road; Gahanna, OH 43230; USA
Telephone Number: (614) 696-5910 or (855) 552-5684 Fax Number: Not available.
Emergency Telephone Number: Not available.
Date Issued: December 24, 2019 Date Revised: December 24, 2019

This SDS complies with the OSHA Hazard Communication Standard 29CFR1910.1200 as revised in May 2012 (GHS). It may not meet requirements in other countries.

SECTION 2 HAZARDS IDENTIFICATION

GHS Signal Word: None.
GHS Classification: Not classified as hazardous
GHS Hazard Statements: None.
GHS Precautionary Statements: Prevention: None. Response: None.
Storage: None. Disposal: None.
Hazards Not Otherwise Classified: None.
GHS Assessment: Approximately < 0.01% of this mixture consists of ingredient(s) of unknown acute toxicity.
Approximately < 0.01% of the mixture consists of ingredient(s) of unknown hazards to the aquatic environment.

SECTION 3 COMPOSITION / INGREDIENTS

Component	CAS Number	EC Number	Concentration
No hazardous components			
<i>Classification: None.</i>			

SECTION 3 COMPOSITION / INGREDIENTS

Other components are non-hazardous, do not significantly contribute to the hazards of the product or do not require disclosure.

Trade Secret Claims: Specific chemical identity and/or exact percentage (concentration) of components has been withheld as a trade secret.

For the full text of the H-Statements mentioned in this Section, see Section 16.

SECTION 4 FIRST AID MEASURES

- First Aid - Eyes: In case of contact, immediately flush eyes with plenty of water for at least 15 minutes. Get medical attention, if irritation develops.
- First Aid - Skin: In the unlikely event that contact causes a reaction, flush area with soap and water and seek medical attention.
- First Aid - Ingestion: If swallowed and feel unwell, call a physician or poison control center. DO NOT induce vomiting unless directed to do so by a physician or poison control center. If victim is fully conscious, give a cupful of water. Never give anything by mouth to an unconscious person.
- First Aid - Inhalation: In the unlikely event that inhalation of product mists causes a reaction, move victim away from source of exposure and into fresh air. See medical attention.
- Important Symptoms / Effects – Acute and Delayed: Mild tissue inflammation.
- Advice to Physician: Treat symptomatically.

SECTION 5 FIRE FIGHTING MEASURES

- Extinguishing Media: Treat surrounding material. Water spray, dry chemical, carbon dioxide, or foam is recommended. Carbon dioxide can displace oxygen. Use caution when applying carbon dioxide in confined spaces.
- Specific Hazards: This product is not flammable. This product may give rise to hazardous vapors in a fire. Vapors/fumes may be irritating, corrosive and/or toxic.
- Protective equipment and procedures for fire-fighters: Wear full protective clothing and self-contained breathing apparatus.
- Additional Advice: None.

SECTION 6 ACCIDENTAL RELEASE MEASURES

- Spill Procedures: Collect and/or wipe up spills with an absorbent towel/material and transfer into suitable containers for recovery or disposal. Finally flush area with water.
- Personal Precautions: No special protective clothing is required.
- Environmental Precautions: No special containment is necessary.

SECTION 7 HANDLING AND STORAGE

- Handling: No special handling is required.
- Storage: Keep container(s) tightly closed. Use and store this material at ambient temperatures away from heat, direct sunlight and hot metal surfaces. Keep away from any incompatible materials (see Section 10).
- Additional Advice: Store in original container. Store as directed by the manufacturer.

SECTION 8 EXPOSURE CONTROLS AND PERSONAL PROTECTION

Occupational Exposure Standards:	Exposure limits are listed below, if they exist.
Crocodile Cloth:	None.
Engineering Control Measures:	Not required under normal conditions of use.
Respiratory Protection:	A NIOSH certified respirator with an organic cartridge may be used under conditions where airborne concentrations are expected to exceed exposure limits.
Hand Protection:	Not required under normal conditions of use.
Eye Protection:	Not required under normal conditions of use.
Body Protection:	Not required under normal conditions of use.

SECTION 9 PHYSICAL AND CHEMICAL PROPERTIES

Physical State:	Liquid mixture impregnated into a poly-viscose non-woven fabric
Color:	White to slightly off-white
Odor:	Characteristic, faint
Odor Threshold:	Not available.
pH:	5.0 - 6.0
Melting Point/Range (°C/°F):	Not available.
Boiling Point/Range (°C/°F):	≥ 100°C / 212°C (based on constituents)
Flash Point (PMCC) (°C/°F):	≥ 96°C / 204.8°C (based on constituents)
Evaporation Rate:	Not available.
Flammability / Explosivity Limits in Air (%):	Not available.
Vapor Pressure:	≤ 23.8 mmHg (25°C) (based on constituents)
Vapor Density (Air = 1):	Not available.
Relative Density:	Not available.
Solubility in Water:	Soluble (based on constituents - liquid mixture)
Partition Coefficient:	Not available.
Autoignition Temperature (°C/°F):	Not available.
Decomposition Temperature (°C/°F):	Not available.
Viscosity:	Not available.
Explosive Properties:	None.
Oxidizing Properties:	None.
Volatile Organic Content (VOC) (g/l):	< 25 g/l (as defined by 40CFR51.100)

SECTION 10 STABILITY AND REACTIVITY

Reactivity:	Product will not undergo additional reaction.
Stability:	Stable under normal storage conditions.
Hazardous Polymerization:	Will not occur.

SECTION 10 STABILITY AND REACTIVITY

Conditions to Avoid:	Contact with incompatible materials, excessive heat.
Incompatibilities:	Strong oxidizing agents, strong acids, strong bases.
Hazardous Decomposition Products:	Oxides of carbon, aliphatic compounds, toxic by-products.

SECTION 11 TOXICOLOGICAL INFORMATION

If available, toxicity data for the product is given; otherwise component data is listed.

Acute Toxicity:	This product is not expected to be appreciably harmful.
Skin Corrosion / Irritation:	The product may be mildly irritating to the skin. Product testing found faint, barely perceptible erythema/irritation.
Serious Eye Damage / Irritation:	The product may be slightly irritating to the eyes.
Respiratory or Skin Sensitization:	The product is not expected to be dermally sensitizing.
Mutagenicity:	This product is not expected to be mutagenic.
Carcinogenicity:	This product is not expected to be carcinogenic.
Reproductive / Developmental Toxicity:	This product is not expected to be reproductively or developmentally harmful.
Chronic/Subchronic Toxicity: Specific Target Organ/Systemic Toxicity – Single Exposure:	This product is not expected to cause organ effects or systemic toxicity upon a single exposure.
Chronic/Subchronic Toxicity: Specific Target Organ/Systemic Toxicity – Repeated Exposure:	This product is not expected to cause organ effects or systemic toxicity upon repeated exposure.
Aspiration Hazard:	This product does not pose an appreciable aspiration hazard.
Additional Information:	None.

SECTION 12 ECOLOGICAL INFORMATION

If available, ecological data for the product is given; otherwise component data is listed.

Acute Ecotoxicity:	This product is not expected to be appreciably harmful to aquatic species.
Mobility:	No data.
Persistence/Degradability:	Expected to be biodegradable.
Bioaccumulation:	Not expected to bioaccumulate in living tissue.
Other adverse effects:	None.

SECTION 13 DISPOSAL CONSIDERATION

Environmental precautions:	No special containment is necessary.
Product Disposal:	Dispose in accordance with all local, state (provincial), and federal regulations.
Container Disposal:	Dispose in accordance with all local, state (provincial), and federal regulations.

SECTION 14 TRANSPORT INFORMATION

DOT (US):

Proper Shipping Name:	Not regulated
UN Number:	None.
Class:	None.
Packaging Group:	None.
Reportable Quantity:	None.
Marine Pollutant:	None.

IATA:

Proper Shipping Name:	Not regulated
UN Number:	None.
Class:	None.
Packing Group:	None.

IMDG:

Proper Shipping Name:	Not regulated
UN Number:	None.
Class:	None.
Packing Group:	None.
Marine Pollutant:	None.

Transportation classifications may vary by container volume and may be influenced by regional or country variations in regulations.

SECTION 15 REGULATORY INFORMATION

US Toxic Substance Control Act:	The components of this product are exempt from the inventory listing requirements of the U.S. Toxic Substances Control Act (TSCA) Chemical Substance Inventory, when used in cosmetic/personal cleaning products.
Canadian Domestic Substance List:	One or more components of this product are not listed on the Canadian Domestic Substance List. Limited quantities may be permitted.
EU REACH:	One or more components of this product may not have been pre-listed or registered under REACH. Limited quantities may be permitted.
TSCA Sec.12(b) Export Notification:	This product does not contain a chemical at or above de minimis concentrations which requires reporting.
Canadian WHMIS Classification:	None. This product has been classified in accordance with the hazard criteria of the CPR and the SDS contains all of the information required by the CPR.
Massachusetts Right-To-Know:	This product does not contain materials subject to disclosure under the Massachusetts Right-To-Know Law.
New Jersey Right-To-Know:	This product does not contain materials subject to disclosure under the New Jersey Right-To-Know Law.
Pennsylvania Right-To-Know:	This product does not contain materials subject to disclosure under the Pennsylvania Right-To-Know Law.

SECTION 15 REGULATORY INFORMATION

California Proposition 65:	This product does not contain materials which the State of California has found to cause cancer, birth defects or other reproductive harm.	
SARA TITLE III-Section 311/312 Categorization (40 CFR 370):	None. (as of 2018, the EPA has adopted GHS hazard classifications)	
SARA TITLE III-Section 313 (40 CFR 372):	This product does not contain materials which are listed in Section 313 at or above de minimis concentrations.	
CERCLA Hazardous Substance (40 CFR 302)	This product does not contain materials subject to reporting under CERCLA and Section 304 of EPCRA.	
Water Hazard Class (WGK):	This product is slightly water-endangering (WGK=1).	
Other Chemical Inventories:	Australia (AICS):	One or more components are not listed.
	China (IECSC):	One or more components are not listed.
	Japan (ENCS):	All components are listed or exempt.
	Korea (KCI):	One or more components are not listed.
	Philippines (PICCS):	One or more components are not listed.
	Taiwan (TCSI):	All components are listed.

SECTION 16 OTHER INFORMATION

NFPA Rating - HEALTH:	1		
NFPA Rating - FIRE:	1		
NFPA Rating - REACTIVITY:	0		
NFPA Rating - SPECIAL:	NONE		
Full text of H-Statements referred to under Section 3:	None.		
SDS Date Issued:	December 20, 2019		
SDS Current Version:	1.0	Version Date:	December 20, 2019
SDS Revision History:	v1.0 Initial version.		
Abbreviations:	GHS:	Globally Harmonized System of Classification and Labeling of Chemicals	
	CAS#:	Chemical Abstract Services Number	
	ACGIH:	American Conference of Governmental Industrial Hygienists	
	OSHA:	Occupational Safety and Health Administration	
	NFPA:	National Fire Protection Association	
	DOT:	US Department of Transportation	
	RCRA:	US Resource Conservation and Recovery Act	
	TLV:	Threshold Limit Value	
	TWA:	Time-Weighted Average	
	PEL:	Permissible Exposure Limit	
	STEL:	Short Term Exposure Limit	
	WEEL:	Workplace Environmental Exposure Levels	
	AIHA:	American Industrial Hygiene Association	
	NTP:	National Toxicology Program	
	IARC:	International Agency for Research on Cancer	
	LD50:	Lethal Dose 50%	
	LC50:	Lethal Concentration 50%	
	NOAEL:	No Observed Adverse Effect Level	
	NOEL:	No Observed Effect Level	

SECTION 16 OTHER INFORMATION

EC50: Effective Concentration 50%
LL50: Lethal Loading Rate 50%
BCF: Bioconcentration Factor
BOD: Biological Oxygen Demand
Koc: Soil Organic Carbon Partition Coefficient.
Tlm: Median Tolerance Limit

Key References: United States National Library of Medicine's TOXNET
Patty's Toxicology, 5th Edition
European Commission's Institute for Health and Consumer Protection
European Chemicals Agency (ECHA)
American Conference of Governmental Industrial Hygienists
International Agency for Research on Cancer
United States National Toxicology Program
United States Occupational Safety and Health Administration
United States Department of Transportation
Supplier Material Safety Data Sheets

Disclaimer: *The data contained herein is based on information that the company believes to be reliable, but no expressed or implied warranty is made with regard to the accuracy of such data or its suitability for a given situation. Such data relates only to the specific product described and not to such products in combination with any other product and no agent of the company is authorized to vary any of such data. The company and its agents disclaim all liability for any action taken or foregone on reliance upon such data.*

Prepared by: ChemOne Compliance, LLC