Issuing Date No data available Revision Date 01-Jan-2018 Revision Number 1



The supplier identified below generated this SDS using the UL SDS template. UL did not test, certify, or approve the substance described in this SDS, and all information in this SDS was provided by the supplier or was reproduced from publically available regulatory data sources. UL makes no representations or warranties regarding the completeness or accuracy of the information in this SDS and disclaims all liability in connection with the use of this information or the substance described in this SDS. The layout, appearance and format of this SDS is © 2014 UL LLC. All rights reserved.

1. IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

Product identifier

Product Name 49870 Surface Cleaning Wipes - Tub

Other means of identification

Synonyms None

Recommended use of the chemical and restrictions on use

Recommended Use Wipes, Cleaning (with Chemical)

Uses advised against No information available

Details of the supplier of the safety data sheet

Supplier Name UAB "Fabrica moderna"

Supplier Address A.Juozapavičiaus pr. 7F,

LT-45251

Kaunas, Lithuania

Supplier Phone Number Phone: +370 682 54054

Supplier Email info@fabrica-moderna

Emergency telephone number

Company Emergency Phone Number +370 682 54054

Toll Free Phone Number 1-800-727-0610

2. HAZARDS IDENTIFICATION

Classification

This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200).



Page 1 / 10

Skin sensitization Category 1

GHS Label elements, including precautionary statements

Emergency Overview

Signal word

Warning

Hazard Statements

May cause an allergic skin reaction



Appearance Clear

Physical state Pre-Moistened Towelette (no free liquids) Solid

Odor Odorless

Precautionary Statements - Prevention

Avoid breathing dust/fume/gas/mist/vapors/spray Contaminated work clothing should not be allowed out of the workplace Wear protective gloves

Precautionary Statements - Response

Specific treatment (see supplemental first aid instructions on this label)

Skin

IF ON SKIN: Wash with plenty of soap and water If skin irritation or rash occurs: Get medical advice/attention Wash contaminated clothing before reuse

Precautionary Statements - Storage

None

Precautionary Statements - Disposal

Dispose of contents/container to an approved waste disposal plant

Hazards not otherwise classified (HNOC)

Not applicable

Unknown Toxicity

0% of the mixture consists of ingredient(s) of unknown toxicity

Other information

Repeated or prolonged skin contact may cause allergic reactions with susceptible persons

Interactions with Other Chemicals

No information available.



Page 2 / 10

3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS No	Weight-%	Trade Secret
Supplier Trade Secret	Proprietary	0.1 - 1	*

^{*}The exact percentage (concentration) of composition has been withheld as a trade secret

4. FIRST AID MEASURES

First aid measures

General Advice Show this safety data sheet to the doctor in attendance.

Eye contact Rinse thoroughly with plenty of water, also under the eyelids. If symptoms persist, call a

physician.

Skin contact Wash with soap and water. May cause an allergic skin reaction. In the case of skin irritation

or allergic reactions see a physician.

Inhalation Remove to fresh air.

Ingestion Rinse mouth immediately and drink plenty of water. Never give anything by mouth to an

unconscious person.

Most important symptoms and effects, both acute and delayed

Most Important Symptoms and

Effects

Itching. Rashes. Hives.

Indication of any immediate medical attention and special treatment needed

Notes to Physician May cause sensitization of susceptible persons. Treat symptomatically.



5. FIRE-FIGHTING MEASURES

Suitable Extinguishing Media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media

CAUTION: Use of water spray when fighting fire may be inefficient.

Specific hazards arising from the chemical

Product is or contains a sensitizer. May cause sensitization by skin contact.

Uniform Fire Code Sensitizer: Solid

Hazardous Combustion Products

Carbon oxides.

Explosion Data

Sensitivity to Mechanical Impact No.

Sensitivity to Static Discharge No.

Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal precautionsAvoid contact with skin, eyes or clothing. Use personal protective equipment as required.

Environmental precautions

Environmental precautions Refer to protective measures listed in Sections 7 and 8.

Methods and material for containment and cleaning up

Methods for containment Prevent further leakage or spillage if safe to do so.

Methods for cleaning up Pick up and transfer to properly labeled containers.



Page 4 / 10

7. HANDLING AND STORAGE

Precautions for safe handling

Handle in accordance with good industrial hygiene and safety practice. Avoid contact with

eyes.

Conditions for safe storage, including any incompatibilities

Storage Keep containers tightly closed in a dry, cool and well-ventilated place. Store locked up.

Keep out of the reach of children.

Incompatible ProductsNone known based on information supplied.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Exposure Guidelines This product, as supplied, does not contain any hazardous materials with occupational

exposure limits established by the region specific regulatory bodies

Appropriate engineering controls

Engineering Measures Showers

Eyewash stations Ventilation systems

Individual protection measures, such as personal protective equipment

Eye/face protection Wear safety glasses with side shields (or goggles).

Skin and body protection Wear protective gloves and protective clothing.

exceeded or irritation is experienced, ventilation and evacuation may be required.

Hygiene Measures Handle in accordance with good industrial hygiene and safety practice.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical and Chemical Properties

Physical state Pre-Moistened Towelette (no free liquids), Solid

Appearance Clear Odor Odorless

Color No information available **Odor Threshold** No information available

Property Values Remarks Method

pHNo data availableNone knownMelting / freezing pointNo data availableNone knownBoiling point / boiling rangeNo data availableNone knownFlash PointNo data availableNone known



Evaporation RateNo data availableNone knownFlammability (solid, gas)No data availableNone known

Flammability Limit in Air

Upper flammability limit

Lower flammability limit

No data available
No data available
No data available

Vapor pressure No data available None known Vapor density No data available None known **Specific Gravity** No data available None known **Water Solubility** Soluble in water None known Solubility in other solvents No data available None known Partition coefficient: n-octanol/waterNo data available None known **Autoignition temperature** No data available None known **Decomposition temperature** No data available None known Kinematic viscosity No data available None known **Dvnamic viscosity** No data available None known

Explosive propertiesNo data available **Oxidizing properties**No data available

Other Information

Softening Point

VOC Content (%)

Particle Size

No data available

No data available

No data available

Particle Size Distribution

10. STABILITY AND REACTIVITY

Reactivity

No data available.

Chemical stability

Stable under recommended storage conditions.

Possibility of Hazardous Reactions

None under normal processing.

Hazardous Polymerization

Hazardous polymerization does not occur.

Conditions to avoid

None known based on information supplied.

Incompatible materials

None known based on information supplied.

Hazardous Decomposition Products

Carbon oxides.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure

Product Information

Inhalation Specific test data for the substance or mixture is not available.

Eye contact Specific test data for the substance or mixture is not available.

Skin contact Specific test data for the substance or mixture is not available.



Page 6 / 10

Ingestion Specific test data for the substance or mixture is not available.

Component Information

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
Supplier Trade Secret	= 481 mg/kg (Rat)	> 1008 mg/kg (Rat)	= 1.23 mg/L (Rat)4 h

Information on toxicological effects

Symptoms Itching. Rashes. Hives.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Sensitization May cause sensitization by skin contact.

Mutagenic Effects No information available.

Carcinogenicity Contains no ingredient listed as a carcinogen.

Reproductive toxicity No information available.

STOT - single exposure No information available.

STOT - repeated exposure No information available.

Chronic Toxicity No known effect based on information supplied.

Target Organ Effects Skin.

Aspiration Hazard No information available.

Numerical measures of toxicity Product Information

The following values are calculated based on chapter 3.1 of the GHS document

ATEmix (oral) 66,667.00 mg/kg ATEmix (inhalation-dust/mist) 334.00 mg/l ATEmix (inhalation-vapor) 2,000.00 ATEmix



12. ECOLOGICAL INFORMATION

Ecotoxicity

The environmental impact of this product has not been fully investigated.

Persistence and Degradability

No information available.

Bioaccumulation

No information available

Other adverse effects

No information available.

13. DISPOSAL CONSIDERATIONS

Waste treatment methods

Disposal methodsThis material, as supplied, is not a hazardous waste according to Federal regulations (40

CFR 261). This material could become a hazardous waste if it is mixed with or otherwise comes in contact with a hazardous waste, if chemical additions are made to this material, or if the material is processed or otherwise altered. Consult 40 CFR 261 to determine whether the altered material is a hazardous waste. Consult the appropriate state, regional, or local

regulations for additional requirements.

Contaminated Packaging Dispose of contents/containers in accordance with local regulations.

California Hazardous Waste Codes 561

14. TRANSPORT INFORMATION

DOTProper Shipping Name
NOT REGULATED
NON REGULATED

Hazard Class N/A

TDG Not regulated

MEX Not regulated

<u>ICAO</u> Not regulated

IATA Not regulated

Proper Shipping Name NON REGULATED

Hazard Class N/A

IMDG/IMO Not regulated

Hazard Class N/A

RID Not regulated



ADR Not regulated

ADN Not regulated

15. REGULATORY INFORMATION

International Inventories

TSCA Complies

DSL All components are listed either on the DSL or NDSL.

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

US Federal Regulations

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

SARA 311/312 Hazard Categories

Acute Health HazardYesChronic Health HazardNoFire HazardNoSudden release of pressure hazardNoReactive HazardNo

CWA (Clean Water Act)

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

CERCLA

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material

US State Regulations

California Proposition 65

This product does not contain any Proposition 65 chemicals.

U.S. State Right-to-Know Regulations

This product does not contain any substances regulated by state right-to-know regulations.

International Regulations

Canada

WHMIS Hazard Class

Not determined

16. OTHER INFORMATION



Page 9 / 10

NFPA Health Hazards 2 Flammability 0 Instability 0 Physical and

Chemical Hazards - HMIS Health Hazards 2 Flammability 0 Physical Hazard 0 Personal Protection

Χ

Prepared By Product Stewardship

23 British American Blvd. Latham, NY 12110 1-800-572-6501

31-Jul-2015

Revision Note No information available

Disclaimer

Revision Date

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet

