

SAFETY DATA SHEET

Genuine Joe® All Purpose Skin Cleanser

Version	Revision Date:	MSDS Number:	Date of last issue: 12/02/2014
1.2	02/10/2015	31606-00003	Date of first issue: 11/24/2014

SECTION 1. IDENTIFICATION

Product name : Genuine Joe® All Purpose Skin Cleanser

Product code : 02105

Manufacturer or supplier's details

Company name of supplier : S.P. RICHARDS CO.

Address : P.O. Box 1266
Smyrna, Georgia 30081-1266

Telephone : 770-436-6881

Emergency telephone : 770-436-6881

Recommended use of the chemical and restrictions on use

Recommended use : Skin-care

Restrictions on use : This is a personal care or cosmetic product that is safe for consumers and other users under normal and reasonably foreseeable use. Cosmetics and consumer products, specifically defined by regulations around the world, are exempt from the requirement of an SDS for the consumer. While this material is not considered hazardous, this SDS contains valuable information critical to the safe handling and proper use of the product for industrial workplace conditions as well as unusual and unintended exposures such as large spills. This SDS should be retained and available for employees and other users of this product. For specific intended-use guidance, please refer to the information provided on the package or instruction sheet.

SECTION 2. HAZARDS IDENTIFICATION

GHS Classification

Not a hazardous substance or mixture.

GHS Label element

Not a hazardous substance or mixture.

Other hazards

None known.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Substance / Mixture : Mixture

Hazardous ingredients

SAFETY DATA SHEET

Genuine Joe® All Purpose Skin Cleanser

Version 1.2 Revision Date: 02/10/2015 MSDS Number: 31606-00003 Date of last issue: 12/02/2014
Date of first issue: 11/24/2014

Chemical Name	CAS-No.	Concentration (%)
Alcohols, C10-16, ethoxylated, sulfates, sodium salts	68585-34-2	>= 1 - < 5
Cocoamidopropyl betaine	61789-40-0	>= 1 - < 5

SECTION 4. FIRST AID MEASURES

- If inhaled : If inhaled, remove to fresh air.
Get medical attention if symptoms occur.
- In case of skin contact : Wash with water and soap as a precaution.
Get medical attention if symptoms occur.
- In case of eye contact : Flush eyes with water as a precaution.
Get medical attention if irritation develops and persists.
- If swallowed : If swallowed, DO NOT induce vomiting.
Get medical attention if symptoms occur.
Rinse mouth thoroughly with water.
- Most important symptoms and effects, both acute and delayed : None known.
- Protection of first-aiders : No special precautions are necessary for first aid responders.
- Notes to physician : Treat symptomatically and supportively.

SECTION 5. FIRE-FIGHTING MEASURES

- Suitable extinguishing media : Water spray
Alcohol-resistant foam
Dry chemical
Carbon dioxide (CO₂)
- Unsuitable extinguishing media : None known.
- Specific hazards during fire fighting : Exposure to combustion products may be a hazard to health.
- Hazardous combustion products : Sulfur oxides
Carbon oxides
Metal oxides
Chlorine compounds
Nitrogen oxides (NO_x)
- Specific extinguishing methods : Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
Use water spray to cool unopened containers.
Remove undamaged containers from fire area if it is safe to do so.

SAFETY DATA SHEET

Genuine Joe® All Purpose Skin Cleanser

Version	Revision Date:	MSDS Number:	Date of last issue: 12/02/2014
1.2	02/10/2015	31606-00003	Date of first issue: 11/24/2014

Evacuate area.

Special protective equipment for fire-fighters : Wear self-contained breathing apparatus for firefighting if necessary.
Use personal protective equipment.

SECTION 6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures	: Follow safe handling advice and personal protective equipment recommendations.
Environmental precautions	: Discharge into the environment must be avoided. Prevent further leakage or spillage if safe to do so. Prevent spreading over a wide area (e.g. by containment or oil barriers). Retain and dispose of contaminated wash water. Local authorities should be advised if significant spillages cannot be contained.
Methods and materials for containment and cleaning up	: Soak up with inert absorbent material. For large spills, provide diking or other appropriate containment to keep material from spreading. If diked material can be pumped, store recovered material in appropriate container. Clean up remaining materials from spill with suitable absorbent. Local or national regulations may apply to releases and disposal of this material, as well as those materials and items employed in the cleanup of releases. You will need to determine which regulations are applicable. Sections 13 and 15 of this SDS provide information regarding certain local or national requirements.

SECTION 7. HANDLING AND STORAGE

Technical measures	: See Engineering measures under EXPOSURE CONTROLS/PERSONAL PROTECTION section.
Local/Total ventilation	: Use only with adequate ventilation.
Advice on safe handling	: Handle in accordance with good industrial hygiene and safety practice. Take care to prevent spills, waste and minimize release to the environment.
Conditions for safe storage	: Keep in properly labeled containers. Store in accordance with the particular national regulations.
Materials to avoid	: Do not store with the following product types: Strong oxidizing agents

SAFETY DATA SHEET

Genuine Joe® All Purpose Skin Cleanser

Version	Revision Date:	MSDS Number:	Date of last issue: 12/02/2014
1.2	02/10/2015	31606-00003	Date of first issue: 11/24/2014

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Ingredients with workplace control parameters

Contains no substances with occupational exposure limit values.

Hazardous components without workplace control parameters

Ingredients	CAS-No.
Alcohols, C10-16, ethoxylated, sulfates, sodium salts	68585-34-2
Cocoamidopropyl betaine	61789-40-0

Engineering measures : Ensure adequate ventilation, especially in confined areas. Minimize workplace exposure concentrations. Dust formation may be relevant in the processing of this product. In addition to substance-specific OELs, general limitations of concentrations of particulates in the air at workplaces have to be considered in workplace risk assessment. Relevant limits include: OSHA PEL for Particulates Not Otherwise Regulated of 15 mg/m³ - total dust, 5 mg/m³ - respirable fraction; and ACGIH TWA for Particles (insoluble or poorly soluble) Not Otherwise Specified of 3 mg/m³ - respirable particles, 10 mg/m³ - inhalable particles.

Personal protective equipment

Respiratory protection : General and local exhaust ventilation is recommended to maintain vapor exposures below recommended limits. Where concentrations are above recommended limits or are unknown, appropriate respiratory protection should be worn. Follow OSHA respirator regulations (29 CFR 1910.134) and use NIOSH/MSHA approved respirators. Protection provided by air purifying respirators against exposure to any hazardous chemical is limited. Use a positive pressure air supplied respirator if there is any potential for uncontrolled release, exposure levels are unknown, or any other circumstance where air purifying respirators may not provide adequate protection.

Hand protection

Remarks : Wash hands before breaks and at the end of workday.

Eye protection : Wear the following personal protective equipment:
Safety glasses

Skin and body protection : Skin should be washed after contact.

Hygiene measures : Ensure that eye flushing systems and safety showers are located close to the working place.
When using do not eat, drink or smoke.
Wash contaminated clothing before re-use.

SAFETY DATA SHEET

Genuine Joe® All Purpose Skin Cleanser

Version	Revision Date:	MSDS Number:	Date of last issue: 12/02/2014
1.2	02/10/2015	31606-00003	Date of first issue: 11/24/2014

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance	: liquid
Color	: opalescent, pink
Odor	: floral
Odor Threshold	: No data available
pH	: 4.8 - 6.2
Melting point/freezing point	: No data available
Solidification / Setting point	2.9 °C
Initial boiling point and boiling range	: 97.00 °C
Flash point	: > 100 °C
Evaporation rate	: No data available
Flammability (solid, gas)	: Not applicable
Upper explosion limit	: No data available
Lower explosion limit	: No data available
Vapor pressure	: No data available
Relative vapor density	: No data available
Density	: 1.00 g/cm ³
Solubility(ies)	
Water solubility	: soluble
Partition coefficient: n-octanol/water	: Not applicable
Autoignition temperature	: No data available
Decomposition temperature	: The substance or mixture is not classified self-reactive.
Viscosity	
Viscosity, kinematic	: 3,000 - 16,000 mm ² /s (20 °C)
Explosive properties	: Not explosive
Oxidizing properties	: The substance or mixture is not classified as oxidizing.

SAFETY DATA SHEET

Genuine Joe® All Purpose Skin Cleanser

Version	Revision Date:	MSDS Number:	Date of last issue: 12/02/2014
1.2	02/10/2015	31606-00003	Date of first issue: 11/24/2014

SECTION 10. STABILITY AND REACTIVITY

Reactivity	: Not classified as a reactivity hazard.
Chemical stability	: Stable under normal conditions.
Possibility of hazardous reactions	: Can react with strong oxidizing agents.
Conditions to avoid	: None known.
Incompatible materials	: Oxidizing agents
Hazardous decomposition products	: No hazardous decomposition products are known.

SECTION 11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure

Inhalation
Skin contact
Ingestion
Eye contact

Acute toxicity

Not classified based on available information.

Product:

Acute oral toxicity	: Acute toxicity estimate: > 5,000 mg/kg Method: Calculation method
---------------------	--

Ingredients:

Alcohols, C10-16, ethoxylated, sulfates, sodium salts:

Acute oral toxicity	: LD50 (Rat): > 2,000 mg/kg Assessment: The substance or mixture has no acute oral toxicity
---------------------	--

Cocoamidopropyl betaine:

Acute oral toxicity	: LD50: > 5,000 mg/kg Method: OECD Test Guideline 401 Remarks: Based on data from similar materials
---------------------	---

Acute dermal toxicity	: LD50 (Rat): > 2,000 mg/kg Method: OECD Test Guideline 402 Assessment: The substance or mixture has no acute dermal toxicity Remarks: Based on data from similar materials
-----------------------	--

Skin corrosion/irritation

Not classified based on available information.

Product:

Result: No skin irritation

SAFETY DATA SHEET

Genuine Joe® All Purpose Skin Cleanser

Version	Revision Date:	MSDS Number:	Date of last issue: 12/02/2014
1.2	02/10/2015	31606-00003	Date of first issue: 11/24/2014

Ingredients:

Alcohols, C10-16, ethoxylated, sulfates, sodium salts:

Result: Skin irritation

Serious eye damage/eye irritation

Not classified based on available information.

Product:

Result: No eye irritation

Ingredients:

Alcohols, C10-16, ethoxylated, sulfates, sodium salts:

Result: Irreversible effects on the eye

Cocoamidopropyl betaine:

Species: Rabbit

Result: Irreversible effects on the eye

Method: OECD Test Guideline 405

Remarks: Based on data from similar materials

Respiratory or skin sensitization

Skin sensitization: Not classified based on available information.

Respiratory sensitization: Not classified based on available information.

Product:

Assessment: Does not cause skin sensitization.

Ingredients:

Cocoamidopropyl betaine:

Test Type: Maximization Test (GPMT)

Routes of exposure: Skin contact

Species: Guinea pig

Result: negative

Remarks: Based on data from similar materials

Germ cell mutagenicity

Not classified based on available information.

Ingredients:

Cocoamidopropyl betaine:

Genotoxicity in vitro : Test Type: Bacterial reverse mutation assay (AMES)
Method: OECD Test Guideline 471
Result: negative
Remarks: Based on data from similar materials

Genotoxicity in vivo : Test Type: Mammalian erythrocyte micronucleus test (in vivo cytogenetic assay)
Species: Mouse
Application Route: Ingestion
Result: negative

SAFETY DATA SHEET

Genuine Joe® All Purpose Skin Cleanser

Version	Revision Date:	MSDS Number:	Date of last issue: 12/02/2014
1.2	02/10/2015	31606-00003	Date of first issue: 11/24/2014

Remarks: Based on data from similar materials

Carcinogenicity

Not classified based on available information.

IARC

No ingredient of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.

OSHA

No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA.

NTP

No ingredient of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.

Reproductive toxicity

Not classified based on available information.

Ingredients:

Cocoamidopropyl betaine:

Effects on fetal development : Test Type: Embryo-fetal development
Species: Rat
Application Route: Ingestion
Method: OECD Test Guideline 414
Result: negative
Remarks: Based on data from similar materials

STOT-single exposure

Not classified based on available information.

STOT-repeated exposure

Not classified based on available information.

Repeated dose toxicity

Ingredients:

Cocoamidopropyl betaine:

Species: Rat
NOAEL: 250 mg/kg
Application Route: Ingestion
Exposure time: 90 d
Method: OECD Test Guideline 408
Remarks: Based on data from similar materials

Aspiration toxicity

Not classified based on available information.

SAFETY DATA SHEET

Genuine Joe® All Purpose Skin Cleanser

Version	Revision Date:	MSDS Number:	Date of last issue: 12/02/2014
1.2	02/10/2015	31606-00003	Date of first issue: 11/24/2014

SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity

Ingredients:

Cocoamidopropyl betaine:

Toxicity to fish : LC50: > 1 - 10 mg/l
Exposure time: 96 h
Method: ISO 7346/2
Remarks: Based on data from similar materials

Toxicity to bacteria : EC50: > 100 mg/l
Method: OECD Test Guideline 209
Remarks: Based on data from similar materials

Persistence and degradability

Product:

Biodegradability : Result: Biodegradable

Ingredients:

Alcohols, C10-16, ethoxylated, sulfates, sodium salts:

Biodegradability : Result: Readily biodegradable.

Cocoamidopropyl betaine:

Biodegradability : Result: Readily biodegradable.
Biodegradation: > 60 %
Exposure time: 28 d
Method: OECD Test Guideline 301
Remarks: Based on data from similar materials

Bioaccumulative potential

No data available

Mobility in soil

No data available

Other adverse effects

No data available

SECTION 13. DISPOSAL CONSIDERATIONS

Disposal methods

Waste from residues : Dispose of in accordance with local regulations.

Contaminated packaging : Dispose of as unused product.
Empty containers should be taken to an approved waste handling site for recycling or disposal.

SAFETY DATA SHEET

Genuine Joe® All Purpose Skin Cleanser

Version	Revision Date:	MSDS Number:	Date of last issue: 12/02/2014
1.2	02/10/2015	31606-00003	Date of first issue: 11/24/2014

SECTION 14. TRANSPORT INFORMATION

International Regulation

UNRTDG

Not regulated as a dangerous good

IATA-DGR

Not regulated as a dangerous good

IMDG-Code

Not regulated as a dangerous good

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

Not applicable for product as supplied.

Domestic regulation

49 CFR

Not regulated as a dangerous good

SECTION 15. REGULATORY INFORMATION

EPCRA - Emergency Planning and Community Right-to-Know

CERCLA Reportable Quantity

This material does not contain any components with a CERCLA RQ.

SARA 304 Extremely Hazardous Substances Reportable Quantity

This material does not contain any components with a section 304 EHS RQ.

SARA 311/312 Hazards : No SARA Hazards

SARA 302 : No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

SARA 313 : This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

US State Regulations

Pennsylvania Right To Know

Water	7732-18-5	70 - 90 %
Alcohols, C10-16, ethoxylated, sulfates, sodium salts	68585-34-2	1 - 5 %
Sodium chloride	7647-14-5	1 - 5 %

New Jersey Right To Know

Water	7732-18-5	70 - 90 %
Alcohols, C10-16, ethoxylated, sulfates, sodium salts	68585-34-2	1 - 5 %
Sodium chloride	7647-14-5	1 - 5 %
Cocoamidopropyl betaine	61789-40-0	1 - 5 %

SAFETY DATA SHEET

Genuine Joe® All Purpose Skin Cleanser

Version 1.2 Revision Date: 02/10/2015 MSDS Number: 31606-00003 Date of last issue: 12/02/2014
Date of first issue: 11/24/2014

California Prop 65

This product does not contain any chemicals known to the State of California to cause cancer, birth, or any other reproductive defects.

The ingredients of this product are reported in the following inventories:

AICS : All ingredients listed or exempt.


Inventories

AICS (Australia), DSL (Canada), IECSC (China), REACH (European Union), ENCS (Japan), ISHL (Japan), KECI (Korea), NZIoC (New Zealand), PICCS (Philippines), NECSI (Taiwan), TSCA (USA)

SECTION 16. OTHER INFORMATION

Further information

NFPA:



HMIS III:

HEALTH	0
FLAMMABILITY	1
PHYSICAL HAZARD	0

0 = not significant, 1 = Slight,
2 = Moderate, 3 = High
4 = Extreme, * = Chronic

Sources of key data used to compile the Material Safety Data Sheet : Internal technical data, data from raw material SDSs, OECD eChem Portal search results and European Chemicals Agency, <http://echa.europa.eu/>

Revision Date : 02/10/2015

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and shall not be considered a warranty or quality specification of any type. The information provided relates only to the specific material identified at the top of this SDS and may not be valid when the SDS material is used in combination with any other materials or in any process, unless specified in the text. Material users should review the information and recommendations in the specific context of their intended manner of handling, use, processing and storage, including an assessment of the appropriateness of the SDS material in the user's end product, if applicable.

US / Z8