

GS 531

Shurtape[®]
TRUE TO YOUR WORK[™]

PREMIUM GRADE FIBERGLASS REINFORCED STRAPPING TAPE

TYPICAL APPLICATIONS

- For heavy duty, maximum security closing, strapping, packaging, protecting, bundling, reinforcing, sealing, unitizing, palletizing and L-Clip applications

PRODUCT FEATURES

- High tensile strength and tear resistance
- Good adhesion, quick stick and shock resistance
- Moisture- and solvent-resistant
- Will not delaminate, split or crack

CONSTRUCTION

Overall Grade/Function: Premium

Backing: Fiberglass reinforced, polyester film (PET)

Adhesive: Synthetic rubber/resin hot melt

STANDARD WIDTH(S)

12 mm 18 mm 24 mm 36 mm 48 mm 96 mm

STANDARD LENGTH(S)

55 m

Contact your Shurtape sales representative for other available sizes


APPLICABLE STANDARDS

ASTM D 5330, Type II; FDA Indirect Contact CFR 21, 175.105; FDA Indirect Contact CFR 21, 177.1520

STORAGE AND USAGE CONDITIONS

Tape should be stored in its original packaging in a cool, dry area away from direct sunlight and should be used within 12 months of date of shipment. Surfaces to which tape is applied should be clean, dry and free of grease, oil or other contaminants.

COLOR(S)



PHYSICAL PROPERTIES

	STANDARD	METRIC
Tensile Strength	300 lbs/in width	525.4 N/10 mm
Adhesion to Stainless Steel	70 oz/in width	7.66 N/10 mm
Thickness	6.7 mils	0.17 mm
Elongation	3.7%	3.7%
Service Temperature Range	-10 F to 150 F	-23 C to 66 C

Physical and performance characteristics shown above are obtained from tests recommended by PSTC, ASTM, government agencies or Shurtape Technologies, LLC, Quality Assurance and Technical Service departments and do not represent a guarantee of product performance. Individual rolls may vary slightly from these averages. The user should determine whether the product is fit for a particular purpose and is suitable for the user's method of application before use.

