

SAFETY DATA SHEET

Issuing Date No data available

Revision Date 01-Jan-2018

Revision Number 1



The supplier identified below generated this SDS using the UL SDS template. UL did not test, certify, or approve the substance described in this SDS, and all information in this SDS was provided by the supplier or was reproduced from publically available regulatory data sources. UL makes no representations or warranties regarding the completeness or accuracy of the information in this SDS and disclaims all liability in connection with the use of this information or the substance described in this SDS. The layout, appearance and format of this SDS is © 2014 UL LLC. All rights reserved.

1. IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

Product identifier

Product Name 56268 250ml Screen Cleaner with Cloth

Other means of identification

Synonyms None

Recommended use of the chemical and restrictions on use

Recommended Use Wipes, Cleaning (with Chemical)

Uses advised against No information available

Details of the supplier of the safety data sheet

Supplier Name UAB "Fabrica moderna"

Supplier Address A.Juozapavičiaus pr. 7F,
LT-45251
Kaunas, Lithuania

Supplier Phone Number Phone: +370 682 54054

Supplier Email info@fabrica-moderna

Emergency telephone number

Company Emergency Phone Number +370 682 54054

Toll Free Phone Number 1-800-727-0610

2. HAZARDS IDENTIFICATION

Classification

This chemical is not considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200).

GHS Label elements, including precautionary statements



Emergency Overview

The product contains no substances which at their given concentration, are considered to be hazardous to health.

Appearance Clear

Physical state Pre-Moistened Towelette
(no free liquids) Solid

Odor Odorless

Precautionary Statements - Prevention

Obtain special instructions before use

Precautionary Statements - Response

None

Precautionary Statements - Storage

None

Precautionary Statements - Disposal

None

Hazards not otherwise classified (HNOC)

Not applicable

Unknown Toxicity

0% of the mixture consists of ingredient(s) of unknown toxicity

Other information

May cause slight eye irritation

Interactions with Other Chemicals

No information available.

3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS No	Weight-%	Trade Secret
Supplier Trade Secret	Proprietary	1 - 5	*

*The exact percentage (concentration) of composition has been withheld as a trade secret

4. FIRST AID MEASURES**First aid measures****Eye contact**

Rinse thoroughly with plenty of water, also under the eyelids. If symptoms persist, call a physician.

Skin contact	Wash with soap and water.
Inhalation	Remove to fresh air.
Ingestion	Rinse mouth immediately and drink plenty of water. Never give anything by mouth to an unconscious person.

Most important symptoms and effects, both acute and delayed

Most Important Symptoms and Effects No information available.

Indication of any immediate medical attention and special treatment needed

Notes to Physician Treat symptomatically.

5. FIRE-FIGHTING MEASURES

Suitable Extinguishing Media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media

CAUTION: Use of water spray when fighting fire may be inefficient.

Specific hazards arising from the chemical

No information available.

Hazardous Combustion Products

Carbon oxides.

Explosion Data

Sensitivity to Mechanical Impact No.

Sensitivity to Static Discharge No.

Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal precautions Avoid contact with eyes.

Environmental precautions

Environmental precautions Refer to protective measures listed in Sections 7 and 8.

Methods and material for containment and cleaning up

Methods for containment Prevent further leakage or spillage if safe to do so.

Methods for cleaning up Pick up and transfer to properly labeled containers.

7. HANDLING AND STORAGE

Precautions for safe handling

Handling Handle in accordance with good industrial hygiene and safety practice. Avoid contact with eyes.

Conditions for safe storage, including any incompatibilities

Storage Keep container tightly closed.

Incompatible Products None known based on information supplied.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Exposure Guidelines

Chemical Name	ACGIH TLV	OSHA PEL	NIOSH IDLH
Supplier Trade Secret	STEL: 150 ppm TWA: 100 ppm S*	TWA: 100 ppm TWA: 600 mg/m ³ (vacated) TWA: 100 ppm (vacated) TWA: 600 mg/m ³ (vacated) STEL: 150 ppm (vacated) STEL: 900 mg/m ³ (vacated) S* S*	IDLH: 600 ppm TWA: 100 ppm TWA: 600 mg/m ³ STEL: 150 ppm STEL: 900 mg/m ³

ACGIH TLV: American Conference of Governmental Industrial Hygienists - Threshold Limit Value OSHA PEL: Occupational Safety and Health Administration - Permissible Exposure Limits NIOSH IDLH Immediately Dangerous to Life or Health

Other Exposure Guidelines Vacated limits revoked by the Court of Appeals decision in AFL-CIO v. OSHA, 965 F.2d 962 (11th Cir., 1992)



Appropriate engineering controls

Engineering Measures	Showers Eyewash stations Ventilation systems
-----------------------------	--

Individual protection measures, such as personal protective equipment

Eye/face protection	No special protective equipment required.
Skin and body protection	No special protective equipment required.
Respiratory protection	No protective equipment is needed under normal use conditions. If exposure limits are exceeded or irritation is experienced, ventilation and evacuation may be required.
Hygiene Measures	Handle in accordance with good industrial hygiene and safety practice.

9. PHYSICAL AND CHEMICAL PROPERTIES**Physical and Chemical Properties**

Physical state	Pre-Moistened Towelette (no free liquids), Solid		
Appearance	Clear	Odor	Odorless
Color	No information available	Odor Threshold	No information available

<u>Property</u>	<u>Values</u>	<u>Remarks</u>	<u>Method</u>
pH	No data available	None known	
Melting / freezing point	No data available	None known	
Boiling point / boiling range	No data available	None known	
Flash Point	No data available	None known	
Evaporation Rate	No data available	None known	
Flammability (solid, gas)	No data available	None known	
Flammability Limit in Air			
Upper flammability limit	No data available		
Lower flammability limit	No data available		
Vapor pressure	No data available	None known	
Vapor density	No data available	None known	
Specific Gravity	No data available	None known	
Water Solubility	Soluble in water	None known	
Solubility in other solvents	No data available	None known	
Partition coefficient: n-octanol/water	No data available	None known	
Autoignition temperature	No data available	None known	
Decomposition temperature	No data available	None known	
Kinematic viscosity	No data available	None known	
Dynamic viscosity	No data available	None known	
Explosive properties	No data available		
Oxidizing properties	No data available		

Other Information

Softening Point	No data available
VOC Content (%)	No data available
Particle Size	No data available
Particle Size Distribution	

10. STABILITY AND REACTIVITY

Reactivity

No data available.

Chemical stability

Stable under recommended storage conditions.

Possibility of Hazardous Reactions

None under normal processing.

Hazardous Polymerization

Hazardous polymerization does not occur.

Conditions to avoid

None known based on information supplied.

Incompatible materials

None known based on information supplied.

Hazardous Decomposition Products

Carbon oxides.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure

Product Information

Inhalation	Specific test data for the substance or mixture is not available.
Eye contact	Specific test data for the substance or mixture is not available.
Skin contact	Specific test data for the substance or mixture is not available.
Ingestion	Specific test data for the substance or mixture is not available.

Component Information

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
Supplier Trade Secret	= 5230 mg/kg (Rat)	= 9500 mg/kg (Rabbit)	-

Information on toxicological effects

Symptoms No information available.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Sensitization No information available.

Mutagenic Effects No information available.

Carcinogenicity Contains no ingredient listed as a carcinogen.

Reproductive toxicity No information available.



STOT - single exposure No information available.

STOT - repeated exposure No information available.

Chronic Toxicity No known effect based on information supplied.

Target Organ Effects None known.

Aspiration Hazard No information available.

Numerical measures of toxicity Product Information

The following values are calculated based on chapter 3.1 of the GHS document
 Not applicable

12. ECOLOGICAL INFORMATION

Ecotoxicity

The environmental impact of this product has not been fully investigated.

Chemical Name	Toxicity to Algae	Toxicity to Fish	Toxicity to Microorganisms	Daphnia Magna (Water Flea)
Supplier Trade Secret		96h LC50: > 10000 mg/L (Pimephales promelas)		48h LC50: = 1919 mg/L

Persistence and Degradability

No information available.

Bioaccumulation

Chemical Name	Log Pow
Supplier Trade Secret	-0.064

Other adverse effects

No information available.

13. DISPOSAL CONSIDERATIONS

Waste treatment methods

Disposal methods This material, as supplied, is not a hazardous waste according to Federal regulations (40 CFR 261). This material could become a hazardous waste if it is mixed with or otherwise comes in contact with a hazardous waste, if chemical additions are made to this material, or if the material is processed or otherwise altered. Consult 40 CFR 261 to determine whether the altered material is a hazardous waste. Consult the appropriate state, regional, or local regulations for additional requirements.

Contaminated Packaging Dispose of contents/containers in accordance with local regulations.



14. TRANSPORT INFORMATION

<u>DOT</u>	NOT REGULATED
Proper Shipping Name	NON REGULATED
Hazard Class	N/A
<u>TDG</u>	Not regulated
<u>MEX</u>	Not regulated
<u>ICAO</u>	Not regulated
<u>IATA</u>	Not regulated
Proper Shipping Name	NON REGULATED
Hazard Class	N/A
<u>IMDG/IMO</u>	Not regulated
Hazard Class	N/A
<u>RID</u>	Not regulated
<u>ADR</u>	Not regulated
<u>ADN</u>	Not regulated

15. REGULATORY INFORMATION

International Inventories

TSCA	Complies
DSL	All components are listed either on the DSL or NDSL.

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory
DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

US Federal Regulations

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

SARA 311/312 Hazard Categories

Acute Health Hazard	No
Chronic Health Hazard	No
Fire Hazard	No
Sudden release of pressure hazard	No
Reactive Hazard	No

CWA (Clean Water Act)

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

CERCLA

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and



Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material

US State Regulations

California Proposition 65

This product does not contain any Proposition 65 chemicals.

U.S. State Right-to-Know Regulations

Chemical Name	New Jersey	Massachusetts	Pennsylvania	Rhode Island	Illinois
Supplier Trade Secret	X	X	X	X	X

International Regulations

Mexico

National occupational exposure limits

Component	Carcinogen Status	Exposure Limits
Supplier Trade Secret (1 - 5)		Mexico: TWA 100 ppm Mexico: TWA 60 mg/m ³ Mexico: STEL 150 ppm Mexico: STEL 900 mg/m ³

Mexico - Occupational Exposure Limits - Carcinogens

Canada

WHMIS Hazard Class

Not determined

16. OTHER INFORMATION

NFPA	Health Hazards 1	Flammability 0	Instability 0	Physical and Chemical Hazards - Personal Protection X
HMIS	Health Hazards 1	Flammability 0	Physical Hazard 0	

Prepared By Product Stewardship
23 British American Blvd.
Latham, NY 12110
1-800-572-6501

Revision Date 31-Jul-2015

Revision Note No information available

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet

