



The Sanitainer brings together superior structural integrity and unique tank design features that are well suited for cleaning and mixing applications.

Sanitainer's unique cylindrical inner tank design eliminates the corners, ribs and seams prevalent in square or rectangular IBCs which are notoriously difficult to clean.

In the past, the expense of cleaning IBCs has seriously eaten into the bottom line profits of companies that reuse these types of tanks. The **Wide Mouth** cylindrical design makes cleaning easier and more cost effective. The large opening provides complete access to the interior of the container for more thorough cleaning and inspection procedures.

Options add to the Sani-tainer's versatility:

- Top lifting lugs allow the use of crane-hook attachments.
- Sanitary valve and fitting connections.
- Anti-teeter bars.
- Permanently molded-in proprietary company, brand or product information.

The Sanitainer is an example of how Bonar Plastics designs products (and responds to special needs) that improve your company's efficiency and effectiveness in sanitary bulk packaging, handling and transportation. That is why we are North America's leading manufacturer of sanitary polyethylene IBCs.



***Email: [sales@bonarplastics.com](mailto:sales@bonarplastics.com)***

***[www.bonarplastics.com](http://www.bonarplastics.com)***

# Features

**100% FDA Compliant PE**

**Construction** - is virtually maintenance free, and easily cleaned and sanitized before use.

**Light weight overall design** can be easily moved or inverted for further inspection or cleaning.

**Unique cylindrical inner tank** design provides superior structural integrity and wide radius corners which optimizes cleanability and mixing.

**2" Sanitary Drain**

Tri-clover clamp connection is easily cleaned, and compatible with most sanitary valves.



**Top Protector** helps align tanks in stacked position and protects top opening from impacts.

**Large Sanitary Lid Opening**

22" lid, clamp and gasket are easily cleaned, and provide complete access to tank interior.



**Retractable Lifting Lugs (optional)** offer superior top-lifting capability via crane or hoist equipment.

**Company or Product name** can be permanently molded in container wall. (optional)

**Heavy duty, premium plastic stacking frame** provides superior stacking strength (3-4 high) and protection for the inner barrel.

**Four Way Forklift** and pallet jack access makes for versatile handling inside and over the road.



Description	Approximate Capacity	Approximate Weight	Length	Width	Height
Sani 240	240 Gals.	242 lbs.	46"	46"	54"
Sani 300	300 Gals.	263 lbs.	46"	46"	62"
Sani 360	360 Gals.	283 lbs.	46"	46"	70"

Material weight rating: 1.0 specific gravity Stacking capacity is 3-4 units high (depending on container size, weight and temperature exposure). Patent #4,847,028 • Other patent pending • Patent #5,490,603 • Patent #4,847,028 • Other patents pending.



6940 "O" Street, Suite 100 • Lincoln, NE • 68510 • Customer Service: 800-768-6246 • Fax: 402-465-1220

Email: sales@bonarplastics.com

Other Manufacturing Locations: Lincoln, NE, Marked Tree, AR, Philippi, WV, Mancelona, MI

Chowchilla, CA • Bensenville, IL

[www.bonarplastics.com](http://www.bonarplastics.com)