

GlobalPure™

761215 Water Filter

Performance Data Sheet

GLOBALPURE™

The GlobalPure™ 761215 filter is *compatible with Global Wall Mounted Water Cooler and Water Bottle Refilling Stations.

* Claim of compatibility verified by manufacturer internal testing.



The 761215 filter is tested and certified by IAPMO R&T Lab and IAPMO R&T to NSF/ANSI Standard 42 for the aesthetic reduction of chlorine, taste and odor, nominal particulate class I and NSF/ANSI Standard 53 for the reduction of lead.

Instructions For Installing Replacement Filters:

1. Turn off water supply; dispense water to relieve pressure.
2. Turn used filter counterclockwise 1/4 turn to remove from filter head.
3. Remove cap from new filter and use to seal used filter.
4. Insert new filter into existing filter head and turn fully clockwise.
5. Turn on water supply and run for a minimum of 10 minutes to purge the filter of air and fine carbon particles.

NSF/ANSI Standard 42

The concentration of the indicated substances in water entering the system was reduced to a concentration less than or equal to the permissible limit for water leaving the system, as specified in NSF/ANSI 42 & 53 and verified and substantiated by test data.

Substance	Influent Challenge Concentration	Percent Reduction Requirement/Maximum Permissible Product Water Concentration	Average % Reduction
Chlorine	2.0 mg/L ± 10%	≥ 50%	99.64%
Particulate, Class I particles 0.5 to < 1 µm	At least 10,000 particles/mL	≥ 85%	99.20%

NSF/ANSI Standard 53

Substance	Influent Challenge Concentration	Percent Reduction Requirement/Maximum Permissible Product Water Concentration	Average % Reduction
Lead pH 6.5	0.15 mg/L ± 10% mg/L	0.010 mg/L	>99.7%
Lead pH 8.5	0.15 mg/L ± 10% mg/L	0.010 mg/L	>99.3%

Not all water will contain contaminants listed. Testing performed under standard laboratory conditions; actual performance may vary. Filter usage must comply with all state and local laws. Filter is only to be used with cold water. Do not use with water that is microbiologically unsafe or of unknown quality without adequate disinfection before or after the system.

Rated Capacity: 3,600 gallons
Rated Service Flow: 1.5 gpm

Operating Pressure: 10 – 105 psi
Operating Temperature: 35 – 100 °F



11 Harbor Park Drive, Port Washington, NY 11050
Customer Service: 1-(800) 645-2986
www.globalindustrial.com