

BD162-0012 Cover Your Cough Compliance Kit



Product Description:

- Kit Includes:
 - FD-062 Respiratory Hygiene Station Locking
 - Holds one hand sanitizer bottle, two boxes of face masks, and one - two boxes of facial tissues
 - Hinged locking lid over face masks and tissues and an adjustable locking lid to secure the hand sanitizer bottle
 - Quartz Beige ABS Plastic and Clear PETG Plastic
 - KS010-0412 Floor Stand
 - Quartz Beige Powder-Coated Steel
 - MP-070 Sign Holder Vertical
 - Holds 8.5" x 11" signage
 - Clear PETG Plastic
- · Assembly hardware included

Primary Area for Product Usage:

- All ports of entry
- · Anywhere respiratory hygiene products are needed

Dispenses:

- Left: Bottles no larger than 3.75"W x 9.00"H x 3.75"D (9.5 cm x 22.9 cm x 9.5 cm)
- Middle: Box(es) no larger than 7.75"W x 9.75"H x 4.75"D (19.7 cm x 24.8 cm x 12.1 cm)
- Right: Box(es) no larger than 5.50"W x 9.75"H x 4.75"D (14.0 cm x 24.8 cm x 12.1 cm)

Product Specifications (overall assembled dimensions):

- 18.50"W x 57.44"H x 17.00"D (47.0 cm x 145.9 cm x 43.2 cm)
- 18.2 lbs (8.3 kg) approximated

Package Specifications:

- · Package Quantity: 1 per case
- 36"L x 20"W x 6"H (91.4 cm x 50.8 cm x 15.2 cm)
- 23.0 lbs (10.4 kg) approximated




BD162-0012


Cover Your Cough Compliance Kit Assembly Instructions

Installation


Always mount dispensers securely prior to loading with product.




To secure base to column, turn column upside down (with top plate down) and place base inverted, as shown, on column.




Use Phillips screwdriver to secure base to column with (4x) screws $(10-32 \times 5/16")$.




Turn stand right side up, so the base is on the floor.



Attach the FD-062 Respiratory Hygiene Station to the column using (4x) screws included with stand. Tighten.



To mount the MP-070 Sign Holder, align the mounting holes of the holder with the holes on the top front of the dispenser. Attach using (2x) barrel screws included with sign holder.



Thumb cutout for signage access goes on the back side.

Parts included:

- Base
- Column
- Respiratory Hygiene Station
- Sign Holder

- Hardware
 - $^{\circ}~$ (8x) 10-32 x 5/16" Phillips head screws
 - o (2x) barrel screws

Tools Required:

Phillips Screwdriver

Flathead Screwdriver



BD162-0012

Cover Your Cough Compliance Kit

Characteristics & Care

FD-062 **ABS Plastic**

KS010-0412 Powder-Coated Steel

MP-070 **PETG Plastic**

Designed for Long-Term, Heavy-Duty **Applications**

The combination of copolymers (Acrylonitrile, Butadiene, and Styrene) gives ABS an excellent combination of strength, rigidity, and toughness.

ABS is chemical and stress-crack resistant. It is tough, dimensionally stable, and will hold up to long-term use. It possesses high strength and performance characteristics at a reasonable cost.

Designed for Long-Term Use

Our steel dispensers and stands are coated with polyester powders which makes them highly resistant to corrosion.

Powder-coated steel is ideal for dispensers used in a healthcare or an industrial setting because it is impact resistant and is not effected by extremes in temperature.

Dispensers and stands made of powder-coated steel are both attractive and functional, providing years of service.

Designed for Long-Term, Heavy-Duty **Applications**

Copolyester resin is designed for heavy-duty applications, and is used by BOWMAN® Dispensers. We never use acrylic in our products.

Copolyester (PETG) is typically 15-20 times tougher than general purpose acrylic. PETG is made to withstand handling and reduce losses due to breakage.

PETG resists a variety of chemicals and commonly used cleaning agents. It is tough and durable (not brittle), providing years of troublefree functionality and long life.

Clear optical characteristics mean the viewer can see the content. read text, and see true colors through the material. It complies with FDA regulations for food contact.

Use mild soap and water to clean. Petroleum-based oils, solvents, and paints should not be used.

Standard hospital cleaning supplies can be used.

For best results, clean by washing the surface with a diluted solution of a mild, non-abrasive detergent in cold or warm water and a nonabrasive cloth. Standard hospital cleaning supplies can be used.

Dry with a soft cloth. Do not use any solvent-based materials, abrasives (e.g. Scotch-brite, steel wool), or apply excessive force during cleaning.

Most cleaning chemicals do not weaken the surface or cause damage to the material. Suggested cleaning method is to use a soft cloth, warm water, and mild soap.