


MODEL: YTX14-BS



Plane Chart:




Parts:

Cover	Container Bottom	Terminal	Positive Plate	Negative Plate	Separator	Electrolyte	Safety Valve	Seal Glue
ABS	ABS	Pb	PbO ₂	Pb	AGM	dilute sulphuric acid	Rubber	Epoxy Resin


Parameter Chart:

Volts	12V	
Capacity (25°C)	10 hours rate	12Ah
Appx.Dimension (mm)	L±2	150
	W±2	87
	H±2	145
Storage Status	Wet	
Weight (Approx)	4.4Kg	
Retention of Charge Storage @25°C		
1 month	97%	Directly Mounted
3 month	90%	Directly Mounted
6 month	80%	Constant Volts:14.4V Limit Current:2.4A Charging Hours:2-3H
12 month	40%	Constant Volts:14.4V Limit Current:2.4A Charging Hours:4-6H
CCA	Factory Standard (-10°C)	Factory Standard (-18°C)
Discharging Current	100A	170A

Discharge Current 25°C



Residual Capacity



*The above are average and data obtained from the first 3 charge/discharge cycles. These are not minimum values.