

BD105-0012 Cover Your Cough Compliance Kit



Product Description:

- Kit Includes:
 - RS005-0412 Respiratory Hygiene Station Locking
 - Holds two boxes of face masks, one two boxes of facial tissues or one box of gloves, and one hand sanitizer dispenser
 - Quartz Beige Powder-Coated Steel
 - KS010-0412 Floor Stand
 - Quartz Beige Powder-Coated Steel
 - MP-070 Sign Holder Vertical
 - Holds 8.5" x 11" signage
 - Clear PETG Plastic
- · Assembly hardware included

Primary Area for Product Usage:

- · All ports of entry
- · Anywhere respiratory hygiene products are needed

Dispenses:

- Left: Dispensing unit no larger than 8.40"W x 14.80"H x 5.00"D (21.2 cm x 37.5 cm x 12.7 cm)
- [Note: Refer to automatic dispensing specifications on detection distance requirements.]
- Middle: Box(es) no larger than 8.00"W x 9.50"H x 4.75"D (20.3 cm x 24.1 cm x 12.1 cm)
- Right: Box(es) no larger than 5.50"W x 9.50"H x 4.75"D (13.7 cm x 24.1 cm x 12.1 cm)

Product Specifications (overall assembled dimensions):

- 22.31"W x 60.51"H x 17.00"D (56.7 cm x 153.7 cm x 43.2 cm)
- 22.4 lbs (10.2 kg) approximated

Package Specifications:

- · Package Quantity: 1 per case
- 36"L x 20"W x 6"H (91.4 cm x 50.8 cm x 15.2 cm)
- 27.0 lbs (12.2 kg) approximated




BD105-0012


Cover Your Cough Compliance Kit Assembly Instructions

Assembly


Always mount dispensers securely prior to loading with product.




To secure base to column, turn column upside down (with top plate down) and place base inverted, as shown, on column.




Use Phillips screwdriver to secure base to column with (4x) screws $(10-32 \times 5/16")$.




Turn stand right side up, so the base is on the floor.



Attach the RS005-0412 Respiratory Hygiene Station to the column using (4x) screws included with stand. One pair of screw holes is located in the hand sanitizer dispener section; the second pair are inside the facemask section and can be accessed with the lid open. Tighten all screws.



To mount the MP-070 Sign Holder, align the mounting holes of the holder with the holes on the top front of the dispenser. Attach using (2x) barrel screws included with sign holder.



Attach hand sanitizer dispenser using VHB tape or mounting holes provided.

Parts included:

- Base
- Column
- · Hygiene Station
- · Sign Holder

- Hardware
 - (8x) 10-32 x 5/16" Phillips head screws
 - o (2x) barrel screws

Tools Required:

Phillips Screwdriver

• Flathead Screwdriver



BD105-0012

Cover Your Cough Compliance Kit Characteristics & Care

RS005-0412 & KS010-0412

Powder-Coated Steel

MP-070 PETG Plastic

Material Characteristics

Designed for Long-Term Use

Our steel dispensers and stands are coated with polyester powders which makes them highly resistant to corrosion.

Powder-coated steel is ideal for dispensers used in a healthcare or an industrial setting because it is impact resistant and is not effected by extremes in temperature.

Dispensers and stands made of powder-coated steel are both attractive and functional, providing years of service.

Designed for Long-Term, Heavy-Duty Applications

Copolyester resin is designed for heavy-duty applications, and is used by BOWMAN® Dispensers. We never use acrylic in our products.

Copolyester (PETG) is typically 15-20 times tougher than general purpose acrylic. PETG is made to withstand handling and reduce losses due to breakage.

PETG resists a variety of chemicals and commonly used cleaning agents. It is tough and durable (not brittle), providing years of trouble-free functionality and long life.

Clear optical characteristics mean the viewer can see the content, read text, and see true colors through the material. It complies with FDA regulations for food contact.

Care and Cleaning

For best results, clean by washing the surface with a diluted solution of a mild, non-abrasive detergent in cold or warm water and a non-abrasive cloth. Standard hospital cleaning supplies can be used.

Dry with a soft cloth. Do not use any solvent-based materials, abrasives (e.g. Scotch-brite, steel wool), or apply excessive force during cleaning.

Most cleaning chemicals do not weaken the surface or cause damage to the material. Suggested cleaning method is to use a soft cloth, warm water, and mild soap.