



MULTISTIRRER

Magnetic Stirrers

Multi-position magnetic stirrer that remains cold even after several days of continuous use.



Robust, Resistant and Reliable

Multi-position magnetic stirrer with stainless steel top for the simultaneous stirring of 6 or 15 positions. Ideal for chemistry, microbiology, biochemistry applications.

- Available in two models for 6 positions of 400 ml and 15 positions of 250 ml
- Speed regulation from 80 to 1500 rpm
- Excellent speed control (electronic), even at low speeds
- Remains cold, even after days of continuous use



INSTRUMENT - CODE

MULTISTIRRER 6	100-240 V / 50-60 Hz	F203A0177
MULTISTIRRER 15	100-240 V / 50-60 Hz	F203A0178

TECHNICAL DATA

	MULTISTIRRER 6	MULTISTIRRER 15
CONSTRUCTION MATERIAL	Epoxy painted metal structure; stainless steel top plate	Epoxy painted metal structure; stainless steel top plate
MODELS	6-position	15-position
STIRRING VOLUME	6 beakers, 400 ml	15 beakers, 250 ml
DISTANCE BETWEEN STIRRING POSITION CENTRES	100 mm	74 mm
ELECTRONIC SPEED REGULATION	From 80 to 1500 rpm	From 80 to 1500 rpm
SPEED CONTROL	Excellent speed control even at low revolutions	Excellent speed control even at low revolutions
STIRRING SYSTEM	High-power driving magnet type "PCM" operated by a mono-phase motor for continuous operation	High-power driving magnet type "PCM" operated by a mono-phase motor for continuous operation
DIMENSION (WXHXD)	230x51.5x370 mm (9.0x2.0x14.4 in)	230x51.5x370 mm (9.0x2.0x14.4 in)
POWER	3.6 W	9 W
WEIGHT	1.75 Kg (3.8 lb)	2.1 Kg (4.6 lb)



We reserve the right to make technical alterations
We do not assume liability for errors in printing, typing or transmission

VELP Official Partner

DESIGNED AND MANUFACTURED IN ITALY



ITALY - HQ
Via Stazione 16
20865 Usmate (MB) Italy
Tel. +39 039 628811
velpitalia@velp.com

INDIA
velpindia@velp.com

USA
155 Keyland Court, Bohemia
NY 11716 - U.S.
Tel. +1 631 573 6002
velpusa@velp.com

CHINA
Xinlong Rd Building 28, Lane 1333
Shanghai city - China
Tel. +86 180 1755 7329
velpchina@velp.com