


# Small Air Receivers / Surge Tanks



These small air receivers / surge tanks are designed for point-of-use air storage. Ideal for providing compressed air for short, peak demand applications.

- ASME Code (except 2 & 3 gallon models)
- 175 PSI Maximum Working Pressure
- Multiple Openings and NPT Thread Sizes
- Plugs Included in All Openings
- Gray Powder Paint Finish



Specifications				Dimensions (inches)									Openings (NPT)				WGT (Lbs.)
Model	Capacity (Gallons)	MAX. PSI	ASME Code	OD	TL	HT	A	B	C	D	E	K	F	G	H	J	
AR8013	2	175	No	6	19	8	4	5.5	4	11	3.5	2	1/2	3/4	3/4	1	14
AR8014	3	175	No	6	25	8	4	8.5	7	11	3.5	2	1/2	3/4	3/4	1	17
AR8015	6	175	Yes	10	20	12	5	5	4	12	6.5	2	1/2	3/4	3/4	1	28
AR8016	10	175	Yes	12	24	14	7	5	6	12	6.5	2	1/2	3/4	3/4	1	37
AR8017	13	175	Yes	12	29	14	7	7.5	8.5	12	6.5	2	1/2	3/4	1 1/2	1	42
AR8018	15	175	Yes	12	33.5	14	7	9.75	10.75	12	6.5	2	1/2	3/4	1 1/2	1	46
AR8019	20	175	Yes	14	32	16	10	6	8	16	8.5	2	1/2	3/4	1 1/2	2	57
AR8020	26	175	Yes	14	41.5	16	10	10.75	12.75	16	10.5	2	1/2	3/4	1 1/2	2	58
AR8021	30	175	Yes	16	37	18	10	8.5	10.5	16	10.5	2	1/2	3/4	1 1/2	2	75