

# GlobalPure™ 761215PF Water Filter Performance Data Sheet

# GLOBALPURE™

The GlobalPure™ 761215PF filter is \*compatible with Global Wall Mounted Water Cooler and Water Bottle Refilling Stations.

\* Claim of compatibility verified by manufacturer internal testing.



The 761215PF filter is tested and certified by IAPMO R&T Lab and IAPMO R&T to NSF/ANSI Standard 42 for the aesthetic reduction of chlorine, taste and odor, nominal particulate class I; NSF/ANSI Standard 53 for the reduction of lead, cyst, turbidity and Total PFAS (PFOA +PFOS, PFNA, PFHxS, and PFHpA); NSF/ANSI Standard 401 for the reduction of Microplastic.

The concentration of the indicated substances in water entering the system was reduced to a concentration less than or equal to the permissible limit for water leaving the system, as specified in NSF/ANSI 42, 53 & 401 and verified and substantiated by test data.

### NSF/ANSI Standard 42

Substance	Influent Challenge Concentration	Percent Reduction Requirement/Maximum Permissible Product Water Concentration	Average % Reduction
Chlorine	2.0 mg/L ± 10%	≥ 50%	98.78%
Particulate, Class I particles 0.5 to < 1 µm	At least 10,000 particles/mL	≥ 85%	98.60%

### NSF/ANSI Standard 53

Substance	Influent Challenge Concentration	Min. Reduction Requirement/Maximum Permissible Product Water Concentration	Average % Reduction
Lead pH 6.5	0.15 mg/L ± 10% mg/L	0.010 mg/L	99.70%
Lead pH 8.5	0.15 mg/L ± 10% mg/L	0.010 mg/L	99.24%
Cyst	min. 50,000/L	99.95%	99.99%
Turbidity	11+/- 1 NTU	0.5 NTU	>99.5%
Total PFAS (PFOA +PFOS, PFNA, PFHxS, and PFHpA)	0.00216+/- 20%	0.010 ug/L	98.05

### NSF/ANSI Standard 401

Substance	Influent Challenge Concentration	Percent Reduction Requirement/Maximum Permissible Product Water Concentration	Average % Reduction
Microplastic	at least 10,000 particles/ml	>/- 85%	98.60%

Not all water will contain contaminants listed. Testing performed under standard laboratory conditions; actual performance may vary. Filter usage must comply with all state and local laws. Filter is only to be used with cold water. Do not use with water that is microbiologically unsafe or of unknown quality without adequate disinfection before or after the system.

Rated Capacity: 3,600 gallons

Rated Service Flow: 1.2 gpm

Operating Pressure: 10 – 80 psi

Operating Temperature: 35 – 100°F



11 Harbor Park Drive, Port Washington, NY 11050

Customer Service: 1-(800) 645-2986

www.globalindustrial.com