



ES

Overhead Stirrers

Overhead stirrer for low viscosity liquids



Resistant and Easy-to-Use

The ES is an intuitive overhead stirrer ensuring safety with overload, over-current and overheating protection.

- Maximum torque of 15 Ncm
- Supports applications with a maximum viscosity of 1000 mPa*s
- Electronic speed regulation from 50 to 1300 rpm, up to 15 L
- Long life, robust motor
- Easy-chuck to change the shafts without tools
- Automatically stops if blocked – no burn-out or damage
- Overload, overcurrent and overtemperature protection
- Sealed to IP 40 standard



INSTRUMENT - CODE

ES

110-230 V / 50-60 Hz

F201A0152

TECHNICAL DATA

CONSTRUCTION MATERIAL	Technopolymer and epoxy painted aluminum alloy
CHUCK RANGE	1 - 10 mm
ELECTRONIC PROTECTION RATING CEI EN 60529	IP 40
ELECTRONIC SPEED REGULATION	From 50 to 1300 rpm
STIRRING VOLUME MAX (H ₂ O)	Up to 15 L
MAX VISCOSITY	1000 (mPa*s)*
TORQUE MAX	15 Ncm
ALLOWED ROOM TEMPERATURE	From 0 to 40 °C
DIMENSION (WXHXD)	80x160x200 mm (3.1x6.3x7.9 in)
POWER	30 W
WEIGHT	1.3 Kg (2.8 lb)



VELP Official Partner

We reserve the right to make technical alterations
We do not assume liability for errors in printing, typing or transmission

DESIGNED AND MANUFACTURED IN ITALY



ITALY - HQ
Via Stazione 16
20865 Usmate (MB) Italy
Tel. +39 039 628811
velpitalia@velp.com

INDIA
velpindia@velp.com

USA
155 Keyland Court, Bohemia
NY 11716 - U.S.
Tel. +1 631 573 6002
velpusa@velp.com

CHINA
Xinlong Rd Building 28, Lane 1333
Shanghai city - China
Tel. +86 180 1755 7329
velpchina@velp.com