




MODEL: Y50-N18L-A3 (GEL)

Plane Chart:

Parts:

Cover	Container Bottom	Terminal	Positive Plate	Negative Plate	Separator	Electrolyte	Gel	Safety Valve	Seal Glue
ABS	ABS	Cu	PbO ₂	Pb	AGM	dilute sulphuric acid	Fumed Silica	Rubber	Epoxy Resin

Parameter Chart:

Volts		12V	
Capacity (25°C)	10 hours rate	21Ah	
Appx. Dimension (mm)	L ± 2	205	
	W ± 2	91	
	H ± 2	159	
Storage Status	Wet		
Weight (Approx)	6.78Kg		
Retention of Charge Storage @25°C			
1 month	97%	Directly Mounted	
3 month	90%	Directly Mounted	
6 month	80%	Constant Volts:14.4V Limit Current:4.2A Charging Hours:2-3H	
12 month	40%	Constant Volts:14.4V Limit Current:4.2A Charging Hours:4-6H	
CCA	Factory Standard (-10°C)	Factory Standard (-18°C)	
Discharging Current	168A	260A	

Discharge Current 25°C

Residual Capacity


★The above are average and data obtained from the first 3 charge/discharge cycles. These are not minimum values.