




CHARACTERISTIC OF VALVE REGULATED FACTORY ACTIVATED LEAD ACID BATTERY

MODEL: YT7B-BS



Parts:

Cover	Container Bottom	Terminal	Positive Plate	Negative Plate	Separator	Electrolyte	Safety Valve	Seal Glue
ABS	ABS	Pb	PbO ₂	Pb	AGM	dilute sulphuric acid	Rubber	Epoxy Resin

Parameter Chart:

Volts	12V	
Capacity (25°C)	10 hours rate	6.5Ah
Appx. Dimension (mm)	L±2	150
	W±2	65
	H±2	94
Storage Status	Wet	
Weight (Approx)	2.15Kg	


Retention of Charge Storage @25°C

1 month	97%	Directly Mounted
3 month	90%	Directly Mounted
6 month	80%	Constant Volts:14.4V Limit Current:1.3A Charging Hours:2-3H
12 month	40%	Constant Volts:14.4V Limit Current:1.3A Charging Hours:4-6H

CCA	Factory Standard (-10 C)	Factory Standard (-18 C)
Discharging Current	50A	80A

★The above are average and data obtained from the first 3 charge/discharge cycles. These are not minimum values.

Discharge Current 25°C



Residual Capacity

