

Quasar®

HIGH SOLIDS FLOOR FINISH

DATA TECH SHEET

PRODUCT DESCRIPTION:

Quasar® is a high solids, metal-crosslinked, water emulsion floor finish. Formulated for outstanding durability, **Quasar®** will outwear conventional finishes under the most demanding traffic and frequent scrubbing conditions. Excellent appearance levels may be achieved in a variety of maintenance programs. Use **Quasar®** on resilient surfaces and sealed wood.

FEATURES:

Durable:

Exceptional resistance to heel marking, scuffing and repeated scrubbing with detergents means that **Quasar®** outwears conventional finishes. Both stripping and recoating cycles are extended, lowering the frequency of these costly procedures.

High Solids Formula:

Maximum labor productivity is assured as you build gloss quickly, with fewer coats.

Superior Soil Resistance:

The tough film of **Quasar®** minimizes soil penetration and surface abrasion even under extreme conditions. Autoscrubbing easily picks up dirt, immediately restoring the shine.

Versatility:

Maintain **Quasar®** using many recognized methods, spray buff, top coat or scrub/recoat.

PRODUCT SPECIFICATIONS:

pH	9.0 ± 0.3
Appearance	Off White Emulsion
Fragrance	Mild polymeric
Freezing Point	About 32°F
Boiling Point	212°F
Solubility in Water	Dispersible
Flash Point	None
Coverage	2500-3000 sq. ft. per gallon
	(may vary due to differences in porosity of the surface)

Slip Resistance: Static coefficient of friction (James Machine) meets or exceeds 0.5 as determined by ASTM D2047-82.

INGREDIENTS:

Water	7732-18-5
Styrene acrylic polymers	Mixture
Diethylene glycol monoethyl ether ...	111-90-0
Tri-butoxyethyl phosphate	78-51-3
Polypropylene emulsion	Mixture
Oxidized polyethylene wax emulsion	68441-17-8

DILUTIONS	HEALTH	FLAMMABILITY	REACTIVITY
CONCENTRATE CONCENTRAR	NFPA 1 HMIS	NFPA 0 HMIS	NFPA 0 HMIS
PROPORCIÓN	SALUD	INFLAMABILIDAD	REACTIVIDAD

0	1	2	3	4
Minimal	Slight	Moderate	Serious	Severe
Mínimo	Mínimo	Moderar	Grave	Drástico

Quasar® HIGH SOLIDS FLOOR FINISH

DIRECTIONS

USE INFORMATION

Recommended on all types of resilient and non-resilient floors which include vinyl composition, rubber, asphalt, quarry, terrazzo and sealed wood floors. NOTE: Old and very porous floors should be sealed with a Franklin sealer prior to application of Quasar®.


INITIAL APPLICATION




CAUTION



1. REMOVE



2. APPLY




3. DRY




4. APPLY


MAINTENANCE



1. DUST MOP



2. Mop



3. BURNISH

INITIAL APPLICATION

1. **REMOVE** old sealer or finish using an appropriate Franklin stripper and following label directions.
2. **APPLY** a thin, even coat of **Quasar®** using a clean finish mop.
3. **DRY:** Allow 20 to 30 minutes of drying time.
4. **APPLY** 2-3 coats for best results allowing for adequate drying time between each coat.

MAINTENANCE

1. **DUST MOP** the floor. Remove gum, labels, and other attached soil deposits with a long-handled scraper or putty knife.
2. **DAMP MOP OR AUTOSCRUB** using a Franklin cleaner. Follow label directions for correct dilution and proper cleaning procedure.
3. **BURNISH** the floor using a soft hair pad and high speed floor machine to remove black scuff marks, scuffs and scrapes.

FIRST AID:

If in eyes or on skin, immediately flush with plenty of water. Get medical attention if irritation persists. If swallowed, get medical attention. NEVER GIVE ANYTHING BY MOUTH TO AN UNCONSCIOUS PERSON.

HANDLING AND STORAGE:

SUGGESTED STORAGE TEMPERATURE: Store inside at 40-90°F. **SPECIAL HANDLING AND STORAGE:** Handle in accordance with good industrial hygiene and safety practices. These practices include avoiding unnecessary exposure and removal of material from eyes, skin and clothing. Store in a cool, dry, ventilated area. **Protect from freezing.** Thoroughly rinse empty containers. **KEEP OUT OF REACH OF CHILDREN.**

PERSONAL PROTECTION:

Respiratory Protection: Not needed in normal use of this product.

Ventilation: Use with adequate ventilation.

Eye Protection: Safety glasses are recommended.

Protective Gloves: Protective gloves are recommended.

Other Protective Clothing or Equipment: Wear clothing as necessary to prevent skin contact.

TRANSPORTATION INFORMATION:

U.S. DOT - Proper Shipping Name: Not regulated by DOT.

Marine Pollutant: No.

MSDS RETRIEVAL
Read MSDS before using this product

800-848-4901

OBTENCIÓN DE HDSM

Leer la HDSM antes de utilizar este producto

FOR CHEMICAL EMERGENCY,
SPILL, LEAK, FIRE, EXPOSURE OR ACCIDENT
CALL CHEMTREC DAY OR NIGHT

800-424-9300

PARA EMERGENCIAS QUÍMICA DERRAMES,
ESCAPES, FUEGO, EXPOSICIÓN O ACCIDENTE
LLAMAR DE DÍA O DE NOCHE A CHEMTREC

TECH HOTLINE
800-810-4829
LÍNEA DE TÉCNICA