




## CHARACTERISTICS OF VALVE REGULATED FACTORY ACTIVATED LEAD ACID BATTERY

### MODEL: YTX4L-BS



### Plane Chart:



### Parts:

Cover	Container Bottom	Terminal	Positive Plate	Negative Plate	Separator	Electrolyte	Safety Valve	Seal Glue
ABS	ABS	Pb	PbO <sub>2</sub>	Pb	AGM	dilute sulphuric acid	Rubber	Epoxy Resin

### Parameter Chart:

Volts	12V	
Capacity (25°C)	10 hours rate	3Ah
Appx. Dimension (mm)	L ± 2	113
	W ± 2	70
	H ± 2	85
Storage Status	Wet	
Weight (Approx)	1.3Kg	


### Retention of Charge Storage @25°C

1 month	97%	Directly Mounted
3 month	90%	Directly Mounted
6 month	80%	Constant Volts:14.4V Limit Current:0.8A Charging Hours:2-3H
12 month	40%	Constant Volts:14.4V Limit Current:0.8A Charging Hours:4-6H

CCA	Factory Standard (-10°C)	Factory Standard (-18°C)
Discharging Current	30A	45A

★ The above are average and data obtained from the first 3 charge/discharge cycles. These are not minimum values.

### Discharge Current 25°C



### Residual Capacity

